

L-com[®]

an INFINIT[®] brand



The L-Com Side Load Wall-Mount Network Rack is an open frame that provides 19-inch wide network equipment to be installed perpendicular to the wall. The sideways open frame rack is offered in 9U, 12U, and 15U heights with a depth of 20.5 inches, and can be used in closets, wiring closets, or anywhere space is limited.

Model	LC-9USDMTWMR	LC-12USDMTWMR	LC-15USDMTWMR	
PHYSICAL				
Rack Capacity (in Rack Units)	9U	12U	15U	
Maximum Rail Depth (in)	20.5	20.5	20.5	
Unit Dimensions (in)	H	21.5	32	
	W	21.5	21.5	
	D	22.1	22.1	
Weight Capacity (kg / lbs)	109 / 240			
Material	Cold Rolled Steel			
Painting / Coating	Black Powder Coating			
Construction	Bolted Assembly			
Rack Hole Type	Square Holes			
ADDITIONAL FEATURES				
Mounting	Wall Mount (Includes 4x M6 Anchors)			
Equipment Mounting Hardware	12x M6 Cage Nut Sets	12x M6 Cage Nut Sets	24x M6 Cage Nut Sets	
Assembly	Assembly Required			
COMPLIANCE AND CERTIFICATIONS				
EIA/ECA-310-E	✓			
ROHS	✓			
CE	✓			
DIN 41494	✓			
IEC-60287-3-100	✓			
SHIPPING				
Shipping Dimensions (in)	L	22.5	27.2	32.5
	W	21.9	22.5	22.5
	H	4.4	4.4	4.4
Shipping Weight (lbs)	35.2	41.8	48.4	