


L-com®

an INFINIT[®] brand



L-Com wall-mount racks are perfect for mounting networking equipment.
 Built from high-quality cold-rolled steel and finished in black powder coating.
 The racks are made to industry specifications, ensuring compatibility with your equipment.

Model/ SKU	LC-6UWMR15IN(12-24)	LC-9UWMR15IN(12-24)	LC-12UWMR15IN(12-24)	LC-15UWMR15IN(12-24)	LC-12UWMR18INH	LC-8-12-22UADJWMR	
PHYSICAL							
Rack Capacity (in Rack Units)	6U	9U	12U	15U	12U	8U/12U/22U	
Rack Depth	16	16	16	16	18	17.5	
Unit Dimensions	H	13.75	19	24	29.5	25	18/24.75/42.5
	W	20	20	20.25	20.25	20.25	20.25
	D	16	16	16	16	18.25	18.25
Weight Capacity (kg/ lbs.)	50/110	50/110	50/110	50/110	68/150	68/150	
Material	Cold Rolled Steel						
Painting/ Coating	Electro-static Powder Coating - Black						
Construction	Bolted	Bolted	Bolted	Bolted	Welded top and bottom frames	Bolted	
Rail Thread Type	Threaded 12-24						
ADDITIONAL FEATURES							
Equipment	(12) 12-24 Screws	(12) 12-24 Screws	(12) 12-24 Screws	(12) 12-24 Screws	(24) 12-24 Screws	(24) 12-24 Screws	
Mounting	Wall Mount (Includes 4 anchors)	Wall Mount (Includes 4 anchors)	Wall Mount (Includes 4 anchors)	Wall Mount (Includes 4 anchors)	Wall Mount (Includes 4 anchors)	Wall Mount (Includes 4 anchors)	
Assembly	Assembly required						
COMPLIANCE AND CERTIFICATIONS							
EIA/CEA-310-E	✓						
ROHS	✓						
CE	✓						
DIN 41494	✓						
IEC-60297-3-100	✓						
SHIPPING							
	L	14.75	20	25	30.5	19.63	37.5
	w	20.75	20.5	27.05	21	4	21.5
Shipping Dimensions (in)	H	7.75	7.75	7.5	7.5	21.45	3
Shipping Weight (lbs.)		16.85	18.7	21.35	23.45	15.35	19.15