

12x10x5 Inch Weatherproof NEMA 4X Enclosure With Blank Aluminum Mounting Plate Applications and Features

Model: NB121005-KIT

Features:

- Molded Fiberglass Reinforced Polyester (FRP) industrial enclosure
- Stainless steel quick release latches with padlock hasps
- NEMA Type 4, 4X / IP66 rated*
- Fully gasketed raised lid & integral mounting flange
- Includes blank aluminum mounting plate

Applications:



- Remote Wireless LAN WiFi equipment installations
- Indoor and outdoor installations
- Rapid Deployment Installations
- Corrosive environments & hotspot applications
- Protection of equipment from theft or damage



Product Description

The NB121005-KIT is a rugged weatherproof enclosure that is ideal for both indoor and outdoor applications. Constructed from molded fiberglass reinforced polyester, it is well suited for high temperature or corrosive environments. The mounting feet allow the enclosure to be wall mounted as well as on a flat surface. The raised lid features a stainless steel continuous hinge and stainless steel quick release latches with padlock hasps. The raised lid is fully gasketed. The enclosure material is UV stabilized and comes in neutral gray color.

The NB121005-KIT includes a Blank Aluminum Mounting Plate permitting free form layout of equipment. The Enclosure and Mounting Plate combination is ideal for custom applications. Mounting stand-offs inside the enclosure are used to secure the Mounting Plate. The contoured body provides an attractive and contemporary appearance. The NB121005-KIT can be used as insulated communications box, terminal wiring box, instrument housing and housing for electrical controls in wet, dusty and corrosive environments.



Model: NB121005-KIT


Specifications

Enclosure Material	Fiberglass Reinforced Polyester	
Enclosure Color	gray (RAL 7036)	
Weight	6.3 lbs (2.85 kg)	
Outside Dimensions (max)	13.31x11.31x5.59 inches (33.82x28.74x14.20 cm)	
Inside Dimensions	12.00x10.00x4.84 inches (30.48x254.00x123.00 cm)	
Aluminum Mounting Plate, Blank	12.00x9.13x0.080 inches 30.8x23.2x0.2 cm	
Flame Rating	UL 94-5V	
RoHS Compliant	Yes	
Ratings*	NEMA 4X / IP65	

*Note: Enclosure ports (Cable conduit connector and N-type holes for lightning protectors or connectors) must be properly sealed to maintain NEMA Type 4, 4X / IP66 rating.

Enclosure and Mounting Plate Dimensions


NB121005 Enclosure



L-com, Inc. 50 High St., West Mill, 3rd Floor, Suite #30 North Andover, MA 01845 www.L-com.com E-mail: sales@L-com.com Phone: 1-800-343-1455 Fax: 1-978-689-9484 © L-com, Inc. All Rights Reserved. L-com Global Connectivity and the L-com logo are registered marks.



Blank Aluminum Mounting Plate (.080 inches thick)



L-com, Inc. 50 High St., West Mill, 3rd Floor, Suite #30 North Andover, MA 01845 www.L-com.com E-mail: sales@L-com.com Phone: 1-800-343-1455 Fax: 1-978-689-9484 © L-com, Inc. All Rights Reserved. L-com Global Connectivity and the L-com logo are registered marks.