

14x12x7 Inch Weatherproof NEMA 4X Enclosure with Blank Starboard Mounting Plate Model: NB141207-KIT01

Applications and Features


Features:

- Molded Fiberglass Reinforced Polyester (FRP) industrial Enclosure
- Stainless steel quick release latches with padlock hasps
- NEMA Type 4, 4X / IP66 rated
- Fully gasketed raised lid & integral mounting flange
- Includes blank, Non-Metallic Starboard mounting plate

Applications:



- Remote Wireless LAN WiFi equipment installations
- Indoor and outdoor installations
- Rapid Deployment Installations
- Corrosive environments & hotspot applications
- Protection of equipment from theft or damage



Product Description

The box is a rugged NEMA Type 4X weatherproof enclosure that is ideal for both indoor and outdoor applications. Constructed from molded fiberglass reinforced polyester, it is well suited for high temperature or corrosive environments. The mounting flange allows it to be wall mounted as well as on a flat surface. The raised lid features a stainless steel continuous hinge and stainless steel quick release latches with padlock hasps. The raised lid is fully gasketed. The enclosure material is UV stabilized and comes in machine tool gray.


This kit is ideal for custom applications, which may require special modifications to the enclosure and mounting plate. The plastic mounting plate allows the radio signals to pass behind the enclosure. This increases the coverage of the radio, when needed in an application.

Specifications

| | |
|----------------------------------|-----------------------------------------------------|
| Enclosure Material | Fiberglass Reinforced Polyester |
| Enclosure Color | Machine Tool Gray |
| Mounting Plate Material | 0.25" (6.35mm) Starboard Polypropylene |
| Mounting Plate Dimensions | 12.7 x 10.8 inches (32.2 x 27.4 cm) |
| Weight | 10.6 lbs (4.8 kg) |
| Outside Dimensions (max) | 15.5 x 13.5 x 7.7 inches (39.3 x 34.2 x 19.5 cm) |
| Inside Dimensions | 13.5 x 11.5 x 5.8 inches (34.3 x 29.2 x 14.7 cm) |
| Flame Rating | UL 94-5V |
| RoHS Compliant | Yes |
| Ratings | NEMA Type 4, 4X / IP66 |

Mounting Plate Dimensions





Enclosure Dimensions

