

20"x16"x11" 120 VAC Vented Industrial Enclosure with Mounting Plate Model: NB201611-10V

Applications

- Remote Wireless LAN WiFi equipment installations
- Indoor and outdoor installations
- Rapid Deployment installations
- Corrosive environments
- Security and surveillance equipment installations

Features

- Molded fiberglass reinforced polyester (FRP) enclosure with integral mounting flanges
- Fully gasketed vented lid with removable filters and stainless steel quick release latches with padlock hasps
- NEMA Type 3R, 3RX / IP24 rated
- Features aluminum mounting plate with surge protected duplex 120 VAC outlets



Description

The NB201611-10V is a rugged weatherproof enclosure that is ideal for both indoor and outdoor applications. Constructed from molded halogen free self extinguishing fiberglass reinforced polyester (FRP), it is well suited for high temperature or corrosive environments. The integral mounting flange allows it to be wall mounted as well as on a flat surface without the need for extra mounting hardware. The fully gasketed lid features a stainless steel continuous hinge and stainless steel quick release latches with padlock hasps. The light grey color of the NB201611-10V is cleaner, cooler and aesthetically pleasing. Users can enjoy the physical benefits of better heat reflection and better UV resistance due to the lighter color. The contoured body provides an attractive and contemporary appearance. Due to the large size of this enclosure, it can accommodate dual sets of most access points.

120 VAC Mounting Plate with Lightning Protection

The aluminum mounting plate features standard surge protected duplex 120 VAC outlets and a terminal block for easy hook up to the externally provided line power.

Vented Enclosure

The NB201611-10V features a vented lid with removable filters and vent covers on the outside of the enclosure.

Optional Pole Mounting Kits

Available on the L-com web site, these optional kits allows the enclosure to be mounted on poles ranging from 1.2 to 11 inches in diameter.

Specifications

Enclosure Material	Halogen free, self-extinguishing fiberglass reinforced polyester (FRP)
Enclosure Color	Light Grey (RAL7035)
Voltage	120 VAC
Weight	22.6 lbs (10.3 kg)
Mounting Plate Material	.10" (2.5mm) Thick Anodized Aluminum
Mounting Plate Dimensions	18.9 x 14.9 in. (479 x 378 mm)
Outside Dimensions (max)	17.3 x 21.3 x 11.6 in. (440 x 541 x 294 mm)
Inside Dimensions	19.7 x 15.7 x 9.7 (plate to cover) in. (500 x 398 x 246 mm)
Flame Rating	UL 94-5V
RoHS Compliant	Yes
Cable Feed	1/2" Cable Conduit Connector
Ratings	NEMA Type 3R, 3RX / IP24



