

14x12x7 Inch Black Weatherproof Industrial Enclosure w/Blank Aluminum Mounting Plate Model: NBB141207-KIT

Applications

- Wireless network and telecommunications equipment installations
- Security and surveillance equipment installations
- Industrial control equipment installations
- Hydraulic or pneumatic control installations
- Indoor and outdoor installations

Features

- Enclosure made from hot compression molded halogen free, self extinguishing fiberglass reinforced polyester
- Stainless steel quick release latch with padlock hasps
- NEMA 4X / IP66-11 rated
- Fully gasketed raised lid and integral mounting flange
- Includes blank aluminum mounting plate



Description

The NBB141207 is a UL® Listed rugged weatherproof enclosure that is ideal for both indoor and outdoor applications. Constructed from molded halogen free self extinguishing fiberglass reinforced polyester, it is well suited for high temperature or corrosive environments. The integral mounting flange allows it to be wall mounted as well as on a flat surface. The fully gasketed raised lid features a stainless steel continuous hinge and a stainless steel quick release latch with padlock hasp.

The black color of the NBB series makes these enclosures ideal for security and surveillance equipment since they blend in easier with existing municipality landscapes. The contoured body provides an attractive and contemporary appearance.

The NBB141207 is ideal for custom applications, which may require special modifications to the enclosure. Contact L-com with your custom requirements and let us provide it for you. Integral mounting stand-offs inside the enclosure can be used for mounting plates. Blank and custom mounting plates are available from L-Com.

The NBB141207-KIT includes a Blank Aluminum Mounting Plate permitting free form layout of equipment. The Enclosure and Mounting Plate combination is ideal for custom applications. Mounting stand-offs inside the enclosure are used to secure the Mounting Plate.

Specifications

Enclosure Specifications

Enclosure Material	Halogen free, self extinguishing fiberglass reinforced polyester
Enclosure Color	Black
Weight	10.6 lbs (4.8 kg)
Outside Dimensions (max)	15.5 x 13.5 x 7.7 in (393 x 342 x 195mm)
Inside Dimensions	13.5 x 11.5 x 7.7 in (343 x 292 x 147mm)
Temperature Ratings	Continuous: -58°F to 302°F (-50°C to 150°C) Momentary exposure up to 392°F (200°C).
UL and CSA Approved	Yes
RoHS Compliant	Yes
NEMA Ratings*	Type 3, 3R, 3S, 4, 4X, 12 and 13
IEC 529 Ratings*	IP66-11

*Ratings prior to modifications

Mounting Plate Specifications

Plate Material	Aluminum
Dimensions	10.8 x 12.7 in. (276 x 324 mm)