

14"x10"x4" Vented OUTDOOR Enclosure Model: NBP141004-40VW

Applications

- Compact weatherproof molded ABS enclosure
- Fully gasketed pad lockable raised lid, vented with rain guards for indoor/outdoor convection cooling
- NEMA Type 3R, 3RX / IP24 rated
- 802.3af compatible PoE interface with Cat 5 surge protection
- Heavy duty hook-and-loop tape for mounting equipment in enclosure

Features

- Remote Wireless LAN WiFi equipment installations using Power-over-Ethernet (PoE)
- Rapid Deployment & indoor/outdoor installations
- Corrosive environments
- Hotspot applications
- Protection of equipment from theft or damage



Description

Secure your wireless equipment...

Remote wireless equipment such as access points, routers and bridges [see below] often are more vulnerable to tampering and theft. This can disrupt and even cripple critical communications. A low cost solution for protecting and securing your wireless equipment is the NBP141004-40VW. This rugged, molded composite enclosure is ideal for indoor/outdoor applications requiring equipment cooling air. The compact size of this enclosure makes it ideal for locations with limited space requirements such as equipment closets or mobile applications. Also due to its size, the NBP141004-40VW can be used where aesthetics are important, such as in offices and in public areas requiring HotSpots.

The 10.5" x 9.5" x 4" (266 x 241 x 101 mm) compartment features an 802.3af compatible PoE interface with Cat 5 Surge Protection. Cable access to the inside of the enclosure is via three rubber cable glands located on the bottom. Equipment can be mounted inside the enclosure either by using the included hook-and-loop tape or the four mounting stand-offs. The raised lid features a continuous gasket and a quick release latch with provisions for a padlock. The vents are protected by an effective rain shield used to keep moist out of the enclosure. The enclosure material is molded UV stabilized ABS. Three gasketed mounting holes are provided inside the enclosure for easy installations.

Specifications

| | |
|----------------------------------|--|
| Power Module Voltage | 12-48 VDC Power-over-Ethernet |
| Enclosure Material | Molded UV Stabilized ABS |
| Enclosure Color | Gray |
| Weight | 4.2 lbs. (1.9kg) |
| Outside Dimensions (Max.) | 14.5 x 10.8 x 4.3 in (36.8 x 27.4 x 10.9 cm) |
| Inside Dimensions | 10.5 x 9.5 x 4 in (26.6 x 24.1 x 10.1 cm) |
| Cable Feed | (3) 9/16" (14.2mm) Rubber Cable Glands |
| Ratings | NEMA Type 3R, 3RX / IP24 |

