





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|------------------------|------------|----------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | REV A DRAWING RELEASED | 11/26/2018 | JYOU |
| | | | |
| | | | |



| | | | | |
|--|--|---|---|---|
| <p>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</p> <p>OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%</p> <p>ALL OTHER DIMENSIONAL TOLERANCES: $.X = \pm .2$ [5.08] $.XX = \pm .02$ [5.1] $.XXX = \pm .005$ [1.3]</p> <p>PROJECTION </p> | <p>APPROVALS</p> <p>DRAWN BY JYOU</p> <p>CHECKED BY BGATES</p> <p>APPROVED BY BGATES</p> | <p>DATE</p> <p>11/02/2018</p> <p>11/02/2018</p> <p>11/02/2018</p> | <p>L-com Global Connectivity</p> <p>50 HIGH STREET NORTH ANDOVER, MA 01845</p> | |
| | <p>CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY</p> | | | <p>CATEGORY</p> <p>RACKMOUNT CABLE</p> |
| | <p>SCALE: NONE</p> | | <p>COLOR VARIATIONS MAY OCCUR</p> | <p>PRODUCT DESCRIPTION</p> <p>L-COM 19" CABLE MANAGEMENT PANEL WITH 5 METAL D-RINGS 1U</p> |
| | <p>SIZE A</p> | <p>FSCM NO. 43321</p> | <p>DWG. NO. RP00010-1</p> | <p>REV. A</p> |