


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING NUMBER WAS 97-101.502	9/14/10	D. CASTRO



NOTES:

1. THIS HOOD MAY BE USED WITH ANY MALE OR FEMALE 25-PIN OR HIGH DENSITY 44-PIN D-SUB CONNECTOR. (NOT SUPPLIED) SUITABLE FOR CABLES WITH DIAMETERS UP TO .35 INCHES (8.9mm)
2. HARDWARE IS INCLUDED TO FIRMLY ATTACH THE CABLE TO ONE OF THE HOOD SECTIONS. THE HOOD SECTIONS SNAP TOGETHER AND THEN ARE SECURED WITH TWO PHILLIPS FLATHEAD SELF-TAPPING SCREWS.
3. HOOD COLOR IS CHROME PLATED, FINISH IS MATTE, EXCEPT FOR LABEL INSERT AREA.
4. HOOD ASSEMBLY IS INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPEC. PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	DRAWN BY D. CASTRO	9/14/10				
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY D. PARHAM	9/14/10	CATEGORY D-SUB			
	APPROVED BY D. FRISIELLO	9/14/10	PRODUCT DESCRIPTION METALLIZED PLASTIC HOOD KIT FOR DB25			
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. SDRS25HOT	REV. A
			SCALE: NONE	CAD FILE: SDRS25HOT.SLDDRW	SHEET 1 OF 1	