


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	09/02/22	GUTTADAURO



TABULATION BLOCK	
ITEM NO.	LENGTH ±.6 [15]
C13LPDC14-15-3F	36.0 [914]
C13LPDC14-15-6F	72.0 [1829]

NOTES:

1. PLUG: TYPE EN60320 C14, BLACK
2. CONNECTOR: EN60320 C13 LOCK PLUS, DOWN-ANGLED, BLACK
3. CORDAGE: SJT3X14AWG, BLACK
COLOR CODING OF CONDUCTOURS: BLACK, WHITE, GREEN
APPROVALS: UL, CSA
RATING: 15A/250V
4. OPTIONAL LABELS MAY INCLUDE UL, CURRENT AND/OR WARNING.
5. CABLE ASSEMBLIES SHALL BE INDIVIDUALLY PACKAGED.

<small>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</small> OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5] FRACTIONS ± 1/32 .XX = ±.02 [5] ANGLES ± 1° .XXX = ±.005 [13]	APPROVALS DRAWN BY VTHANGARAJ CHECKED BY DGUST APPROVED BY GUTTADAURO	DATE 09/02/22 09/02/22 09/02/22	 an INFINITO brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY POWER PRODUCTS PRODUCT DESCRIPTION IEC LOCK C13+ DOWN TO C14, 15A, 250V		
THIRD-ANGLE PROJECTION 	SIZE A	CAGE CODE 43321	ITEM NO. C13LPDC14-15	REV. A
SCALE: NONE		CAD FILE: C13LPDC14-15.SLDDRW		SHEET 1 OF 1