


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/1/12	D.GRIFFIN
B	ECN 6451: UPDATED NOTES & WIRING MAP. CHANGED EXPOSED CONN. DIM.	10/10/12	D. DESJARDIN
B	ECN 99999: UPDATE TO CORRECT ORIENTATION OF LOGO ON MINI END	1/26/16	S.LI




"P1"
5-PIN MINI B USB PLUG
RIGHT ANGLE RIGHT
CONTACTS: 30 μINCHES
GOLD PLATING

"P2"
SERIES "A" USB PLUG
CONTACTS: 30 μINCHES
GOLD PLATING

ONE 28AWG STRANDED TINNED COPPER TWISTED PAIR
TWO 28AWG STRANDED TINNED COPPER CONDUCTORS
OVERALL ALUMINIZED POLYESTER SHIELD WITH DRAIN WIRE
PLUS TINNED COPPER BRAID SHIELD.
PVC OUTER JACKET, BLACK

MODEL NUMBER	LENGTH METERS [FEET]
CAA-90RMB5-03M	.3 [.98]
CAA-90RMB5-05M	.5 [1.64]
CAA-90RMB5-075M	.75 [2.46]
CAA-90RMB5-1M	1.0 [3.28]
CAA-90RMB5-2M	2.0 [6.56]
CAA-90RMB5-3M	3.0 [9.84]
CAA-90RMB5-5M	5.0 [16.41]



△
NOTES:

1. CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.
2. CABLE ASSEMBLY SHALL MEET USB 2.0 REQUIREMENTS.
3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D.FRISIELLO	5/17/11		CATEGORY
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ± .005 [13]	CHECKED BY D.CASTRO	5/17/11	PRODUCT DESCRIPTION	
PROJECTION	APPROVED BY S.SMITH	5/17/11	CA USB STR A/90RT MB5	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
			DWG. NO. CAA-90RMB5	REV. B
			SCALE: NONE	CAD FILE: CAA-90RMB5.SLDDRW
			SHEET 1 OF 1	