



LENGTH CODE CHART		
CABLE# & LENGTH	LENGTH SYMBOL	EXAMPLES OF PART# USED
CA-RTPNFBAXXX	WHERE XXX = LENGTH IN FEET	CA-RTPNFBA010 (10 FEET)
CA-RTPNFBANXX	WHERE NXX = LENGTH IN INCHES	CA-RTPNFBAN16 (16 INCHES)
CA-RTPNFBAMXX	WHERE MXX = LENGTH IN METERS	CA-RTPNFBAM07 (7 METERS)
CA-RTPNFBAXMX	WHERE XMX = LENGTH IN DECIMEL METERS	CA-RTPNFBA3M5 (3.5 METERS)

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY
2. CABLE ASSEMBLY SHALL RECIEVE INSERTION LOSS TEST#TP-0027
3. CABLE ASSEMBLY SHALL WITHSTAND PULL TEST OF 40lbs WITHOUT ANY SEPERATION OR ELECTRICAL FAILURE
4. CABLE SHALL BE RoHS COMPLIANT
5. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031
6. CENTER PIN OF CONNECTORS TO BE SOLDERED OR CRIMPED ONTO CABLE INNER CONDUCTOR

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES <u>OVERALL CABLE LENGTH TOLERANCE</u> ≤ 12 [305] = +1 [25]/-0 >12 [305] ≤ 60 [1524] = +2 [51] /-0 >60 [1524] ≤ 120 [3048] = +4/-0 >120 [3048] U+2264300 [7620] = +6/-0 >300 [76290] = +5%/-0					SIZE A	TITLE: FABRICATION: CA-195R SERIES RP-TNC PLUG TO N-FEMALE BULKHEAD ASSEMBLY with HEATSHRINK			
	C	HL_4177	08/11/09	Changed Length Reference Points To Outside Ends of Connectors		DRAWN BY B.Puchaski 08/11/09 ORIGINATOR B.Puchaski 08/19/08 APPROVAL M. Audus 08/11/09 SCALE 1:1	DRAWING No. F972 PART No. CA-RTPNFBAN	REV C	FILE No. F972-01
	B	HL-ECN-0037	05/11/09	Change Tol. for Heatshrink from ±.06" & ±.15mm					
		REV	ECN No.	DATE	DESCRIPTION				



Website: www.L-com.com
 Tel: 1-800-343-1455
 Copyright © 2009 L-com, Inc.
 All rights reserved.