



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 11303: REVISE UL21149 TO UL20276	09/03/2021	GUTTADAURO




2X eSERIAL ATA RECEPTACLE, 7 PIN CONNECTOR



"J1"



"J2"



UL20276, SERIAL ATA 26AWG PVC, BLACK

2X MOLDED HOOD PVC, BLACK



PART #	LENGTH	
	INCHES	METERS
CAESA-05M	19.68	0.5
CAESA-1M	39.37	1.0
CAESA-2M	78.74	2.0

NOTES:

- CABLE ASSEMBLY SHALL BE SUBJECTED TO A CONTINUITY TEST.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN A CLEAR POLY BAG AND LABELED PER L-COM SPECIFICATION LSP-010.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936				
	DRAWN BY E.STAUBLE	09/25/2008		CATEGORY HETEROGENEOUS			
THIRD-ANGLE PROJECTION 	CHECKED BY D.PARHAM	09/25/2008	PRODUCT DESCRIPTION CBL,ESATA/ESATA				
	APPROVED BY S.SMITH	09/25/2008	<table border="1"> <tr> <td>SIZE A</td> <td>CAGE CODE 43321</td> <td>ITEM NO. CAESA-XM</td> <td>REV. E</td> </tr> </table>	SIZE A	CAGE CODE 43321	ITEM NO. CAESA-XM	REV. E
SIZE A	CAGE CODE 43321	ITEM NO. CAESA-XM	REV. E				
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SCALE: NONE CAD FILE: CAESA-XM.SLDDRW SHEET 1 OF 1				