


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY
	A	INITIAL RELEASE	01/16/2023	HBAKKE	GUTTADAURO





Pin	Wire	Color	Function
1	1	BLACK	POWER L +12V
14	14	1	INNER SHIELD
2	25	WHITE	Tx DATA 0-
15	12	RED	Tx DATA 0+
3	24	WHITE	Tx DATA 1-
16	11	BLUE	Tx DATA 1+
4	23	WHITE	Tx DATA 2-
17	10	GREEN	Tx DATA 2+
5	22	WHITE	XCLK-
18	9	YELLOW	XCLK+
6	21	WHITE	Tx DATA 3-
19	8	VIOLET	Tx DATA 3+
7	20	RED	SerTC+
20	7	BLACK	SerTC-
8	19	BLACK	SerTFG-
21	6	BLUE	SerTFG+
9	18	BLACK	CC1-
22	5	GREEN	CC1+
10	17	YELLOW	CC2+
23	4	BLACK	CC2-
11	16	BLACK	CC3-
24	3	VIOLET	CC3+
12	15	WHITE	CC4+
25	2	BLACK	CC4-
13	13	2	INNER SHIELD
26	26	WHITE	POWER L +12V
		HOUSING	OUTER SHIELD

UL20276 11 TWIST PAIR 30AWG STRANDED TINNED COPPER
 2 CONDUCTOR 28AWG (UNINSULATED) PLUS
 2 CONDUCTOR 28AWG
 JACKET: PVC, GRAY

PART NUMBER	LENGTH	
	FEET	METERS
CLCA03HF-1M	3.28	1.0
CLCA03HF-3M	9.84	3.0
CLCA03HF-5M	16.40	5.0
CLCA03HF-8M	26.25	8.0

- NOTES:
- CABLE SHALL BE TESTED FOR CONTINUITY.
 - CABLE SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
 - FLEX RATED FOR 1,000,000 CYCLES.

REGULATORY COMPLIANCE:
 EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS DRAWN BY HBAKKE CHECKED BY DMAY APPROVED BY GUTTADAURO	DATE 01/16/2023 01/16/2023 01/16/2023	 an INFINITO brand	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321
SCALE: NONE		CAD FILE: clca03hf.SLDDRW		SHEET 1 OF 1