


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
G	ECN #3382: UPDATED DWG FORMAT, ADDED WIRING MAP, REVISED MODEL	6/9/08	E. STAUBLE
H	ECN 4474: ADDED 1.0 FT LENGTH, UPDATED FORMAT, CHANGED NOTES, RoHS	1/7/10	D. CASTRO
J	ECN4813: ADDED 26AWG & PANTONE 400C TO CABLE DESCRIPTION, ADDED LOGO NOTE.	6/9/10	DFP



WIRING MAP					
"P1"	WIRE COLOR	"P2"	"P1"	WIRE COLOR	"P2"
1	BROWN	1	20	GRAY / GREEN	20
2	RED	2	21	GRAY / RED	21
3	ORANGE	3	22	GRAY / VIOLET	22
4	YELLOW	4	23	LIGHT GREEN / BLACK	23
5	GREEN	5	24	RED/BLACK	24
6	BLUE	6	25	ORANGE / BLACK	25
7	VIOLET	7	26	YELLOW / BLACK	26
8	GRAY	8	27	GREEN / BLACK	27
9	WHITE	9	28	LIGHT BLUE / BLACK	28
10	LIGHT GREEN	10	29	LIGHT BLUE / BROWN	29
11	BLACK	11	30	LIGHT BLUE / VIOLET	30
12	GRAY / BLACK	12	31	LIGHT BLUE / RED	31
13	BLUE / WHITE	13	32	LIGHT BLUE	32
14	VIOLET / WHITE	14	33	PINK	33
15	BROWN / WHITE	15	34	PINK / BLACK	34
16	BLACK / WHITE	16	35	PINK / GREEN	35
17	RED / WHITE	17	36	PINK / VIOLET	36
18	ORANGE / WHITE	18	37	PINK / RED	37
19	GREEN / WHITE	19	SHELL	DRAIN WIRE	SHELL

MODEL NUMBER	LENGTH	
	FEET	METERS
CS2N37MM-1	1.0	0.31
CS2N37MM-2.5	2.5	0.76
CS2N37MM-5	5.0	1.52
CS2N37MM-10	10.0	3.05
CS2N37MM-15	15.0	4.57
CS2N37MM-25	25.0	7.62
CS2N37MM-50	50.0	15.24

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPEC. PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [1524] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	APPROVALS TJC CHECKED BY DFP APPROVED BY RC	DATE 9/28/01 9/28/01 10/3/01	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY D-SUBMINIATURE
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	PRODUCT DESCRIPTION CABLE, DB37M/M DBL SHLD
	SCALE: NONE		FSCM NO. 43321	DWG. NO. CS2N37MM
CAD FILE: CS2N37MM.SLDDRW			REV. J	
SHEET 1 OF 1				