


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY
	A	INITIAL RELEASE	01/16/2023	HBAKKE	GUTTADAURO



UL20276 11 TWIST PAIR 30AWG STRANDED TINNED COPPER  
 2 CONDUCTOR 28AWG (UNINSULATED) PLUS  
 2 CONDUCTOR 28AWG  
 JACKET: PVC, GRAY

1	1	BLACK	POWER L +12V
14	14	1	INNER SHIELD
2	25	WHITE	Tx DATA 0-
15	12	RED	Tx DATA 0+
3	24	WHITE	Tx DATA 1-
16	11	BLUE	Tx DATA 1+
4	23	WHITE	Tx DATA 2-
17	10	GREEN	Tx DATA 2+
5	22	WHITE	XCLK-
18	9	YELLOW	XCLK+
6	21	WHITE	Tx DATA 3-
19	8	VIOLET	Tx DATA 3+
7	20	RED	SerTC+
20	7	BLACK	SerTC-
8	19	BLACK	SerTFG-
21	6	BLUE	SerTFG+
9	18	BLACK	CC1-
22	5	GREEN	CC1+
10	17	YELLOW	CC2+
23	4	BLACK	CC2-
11	16	BLACK	CC3-
24	3	VIOLET	CC3+
12	15	WHITE	CC4+
25	2	BLACK	CC4-
13	13	2	INNER SHIELD
26	26	WHITE	POWER L +12V
		HOUSING	OUTER SHIELD



PART NUMBER	LENGTH	
	FEET	METERS
CLCA03HF-1M	3.28	1.0
CLCA03HF-3M	9.84	3.0
CLCA03HF-5M	16.40	5.0
CLCA03HF-8M	26.25	8.0

NOTES:

1. CABLE SHALL BE TESTED FOR CONTINUITY.
2. CABLE SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
3. FLEX RATED FOR 1,000,000 CYCLES.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS ± 1/32 .XX = ± .02 [.5]   ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY HBAKKE	01/16/2023	
	APPROVED BY GUTTADAURO	01/16/2023	CATEGORY <b>AUDIO/VIDEO</b>
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	PRODUCT DESCRIPTION Camera Link Machine Vision High Flex Cable Assembly, PoCL, SDR26 male to SDR26 male, UL20276 PVC, Gray
	SIZE <b>A</b>	CAGE CODE <b>43321</b>	ITEM NO. <b>CLCA03HF</b>
	SCALE: NONE	CAD FILE: clca03hf.SLDDRW	REV. <b>A</b>