


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
D	ECN 6436: UPDATED LOGOS	9/28/12	D. DESJARDIN
E	ECN 9708: UPDAT UL# AND MARKING FOR CABLE	02/22/19	SLI



MODEL #	LENGTH	
	FEET	METERS
CVR3MM-2	2.0	0.61
CVR3MM-3	3.0	0.91
CVR3MM-6	6.0	1.83
CVR3MM-9	9.0	2.74
CVR3MM-12	12.0	3.66
CVR3MM-25	25.0	7.62

- NOTES:
- L-COM LOGO REQUIRED ON BOTH SIDES OF MOLDED HOODS AND STRAIN RELIEFS.
 - CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ± .005 [1.27]	APPROVALS DRAWN BY C.MCCORMICK CHECKED BY D.PARHAM APPROVED BY R.CARRICK	DATE 07/14/2003 07/14/2003 07/14/2003	50 HIGH STREET NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY AUDIO/VIDEO		PRODUCT DESCRIPTION CA, 3 RCA PLUG TO 3 RCA PLUG
PROJECTION 	SIZE A	FSCM NO. 43321	DWG. NO. CVR3MM	REV. E
SCALE: NONE		CAD FILE: CVR3MM.SLDDRW		SHEET 1 OF 1