




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
G	ECN 4564: ADDED ROHS, UPDATED DRAWING AND NEW FORMAT	03/03/2010	DFRISIELLO
H	ECN 5937: ADDED NOTE FOR PANEL MOUNTING	01/24/2010	AD
J	CHANGE DIM FROM .623 TO .541 IN ZONE C6	04/12/2019	GUITTADAURO
K	ECN 10934: REVISED GENDER CHANGER TO SOCKET SAVER IN LABEL NOTE	01/21/2022	MBLACKWOOD




RECOMMENDED PANEL OPENING  
(MAX PANEL THICKNESS: 0.06")

NOTE: DIFFERENT STANDOFFS AND JACK SCREWS  
ARE REQUIRED FOR PANEL MOUNTING.  
SEE WWW.L-COM.COM OR MASTER CATALOG FOR DETAILS.



POSITION 1

78 PIN FEMALE  
HIGH DENSITY  
D-SUB CONNECTOR



JACKSCREW  
SPECIFICATION

NOTES:

MATERIAL:  
SHELL: STEEL  
CONTACTS: COPPER ALLOY  
HARDWARE: BRASS  
INSULATOR: PBT FIBER REINFORCED (UL94V-0 RATED)



FINISH:  
SHELL: TIN/NICKEL PLATED  
CONTACTS: GOLD FLASH PLATED  
HARDWARE: NICKEL PLATED

ELECTRICAL:  
CURRENT RATING: 3 AMP

MISCELLANEOUS:  
OPERATING TEMPERATURE RANGE: -55°C TO +105°C.  
ALL CONTACTS ARE WIRED STRAIGHT THROUGH.  
COMPONENT SHALL BE TESTED FOR CONTINUITY.

LABELING:  
PANTONE 2945 BLUE, "L-COM" FONT MyriaMM REGULAR,  
"SOCKET SAVER" FONT ARIAL BOLD, TEXT HEIGHTS: .085"  
TEXT COLOR: WHITE.

PACKAGING:  
COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN  
ACCORDANCE WITH L-COM SPECIFICATION PS-0031.




PIN 1

78 PIN MALE  
HIGH DENSITY  
D-SUB CONNECTOR



UNLESS OTHERWISE SPECIFIED,  
DIMENSIONS ARE IN INCHES (mm).  
OVERALL CABLE LENGTH TOLERANCE:  
≤12 [305] = ±1 [25] / -0  
>12 [305] ≤60 [1524] = +2 [51] / -0  
>60 [1524] ≤120 [3048] = +4 [102] / -0  
>120 [3048] ≤300 [7620] = +6 [152] / -0  
>300 [7620] = +5% / -0

ALL OTHER DIMENSIONAL TOLERANCES:  
.XX = ±.02 [5] FRACTIONS ± 1/32  
.XXX = ±.005 [13] ANGLES ± 1°



APPROVALS	DATE
D.PARHAM	03/01/2002
CHECKED BY T.CLAIRE	11/08/2001
APPROVED BY R.CARRICK	03/01/2002



CATEGORY  
D-SUBMINIATURE

PRODUCT DESCRIPTION  
ADPT, SKT SAVER HD78 SLIM M/F

SIZE B	CAGE CODE 43321	ITEM NO. DGBH78MF	REV. K
-----------	--------------------	----------------------	-----------

SCALE: NONE CAD FILE: DGBH78MF.SLDRAW SHEET 1 OF 1