


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

| REVISIONS | | | |
|-----------|--|----------|-------------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | CN RELEASE | 10/9/08 | D.GRIFFIN |
| B | ECN 3669: CHG WIRE #14 FROM BLBK/BROWN TO BROWN/WHITE | 10/27/08 | D.FRISIELLO |
| B | ECN 99999: REPAIRED MOLDED BOOT AND SCREWS | 10/29/08 | D.FRISIELLO |
| C | ECN 4474: ADDED 1.0 FT LENGTH, UPDATED FORMAT, CHANGED NOTES | 1/7/10 | D. CASTRO |



| WIRING MAP | | |
|------------|-------------|-------|
| "P1" | WIRE COLOR | "J1" |
| 1 | BLACK | 1 |
| 2 | BROWN | 2 |
| 3 | RED | 3 |
| 4 | ORANGE | 4 |
| 5 | YELLOW | 5 |
| 6 | GREEN | 6 |
| 7 | BLUE | 7 |
| 8 | PURPLE | 8 |
| 9 | GRAY | 9 |
| 10 | WHITE | 10 |
| 11 | PINK | 11 |
| 12 | LIGHT GREEN | 12 |
| 13 | BLACK/WHITE | 13 |
| 14 | BROWN/WHITE | 14 |
| 15 | RED/WHITE | 15 |
| SHELL | DRAIN WIRE | SHELL |

| PART NUMBER | LENGTH | |
|---------------|--------|--------|
| | FEET | METERS |
| CSMNB15MF-1 | 1.0 | 0.31 |
| CSMNB15MF-2.5 | 2.5 | .76 |
| CSMNB15MF-5 | 5.0 | 1.52 |
| CSMNB15MF-10 | 10.0 | 3.05 |
| CSMNB15MF-15 | 15.0 | 4.57 |
| CSMNB15MF-25 | 25.0 | 7.62 |
| CSMNB15MF-50 | 50.0 | 15.24 |

- NOTES:**
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPEC. PS-0031.

| | | | | |
|---|----------------------------|------------------|--|--|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% | APPROVALS | DATE | | 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845 |
| | DRAWN BY D.FRISIELLO | 10/8/08 | | CATEGORY D-SUBMINIATURE |
| ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005 | CHECKED BY D.FORTIN | 10/8/08 | PRODUCT DESCRIPTION CABLE, DB15M/F MOLDED BLK | |
| PROJECTION | APPROVED BY S.SMITH | 10/8/08 | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | |
| | COLOR VARIATIONS MAY OCCUR | SIZE A | FSCM NO. 43321 | DWG. NO. CSMNB15MF |
| | | SCALE: NONE | CAD FILE: CSMNB15MF.SLDDRW | REV. C |
| | | | | SHEET 1 OF 1 |