

6

5

4

3

2

1

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	B	ECO-14977	09/24/2025	Admin	DGUST

F


E

D

C

B

A



PIN ASSIGNMENT			
P1(DP/M)	COLOR	P2(HDMI/F)	
1	RD	1	WITH AL FOIL
3	WT	3	
5	D	5	WITH AL FOIL
7	GN	7	
9	WT	9	WITH AL FOIL
11	D	11	
4	BN	4	WITH AL FOIL
6	WT	6	
2	D	2	WITH AL FOIL
10	BL	10	
12	WT	12	WITH AL FOIL
8	D	8	
13	YL	13	WITH AL FOIL
14	PL	14	
15	BK	15	WITH AL FOIL
17	WT	17	
16	D	16	
18	GN	18	
19	D	19	
20	RD	20	

#### TEST CONDITIONS:

- 100% OPEN, SHORT AND SWAP TEST.
- ON-RESISTANCE: 2 OHMS MAX.
- INSULATION RESISTANCE: 10 MEGAOHM MIN/DC300V/10MS (WIRE END)
- 100% MACHINE TEST, AND TESTED BY APPLE COMPUTER OR APPLE MAC BOOK MONITOR WITH MAC MINI 2014 OR DESKTOP WITH RESOLUTION SUPPORT 4K@60HZ.

#### NOTE:

- ALL MARKINGS ARE FOR REFERENCE ONLY.
- PRODUCT SHALL BE INDIVIDUALLY PACKAGED.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [ ] ARE MILLIMETERS	
TOLERANCES:	
X = ±.2 [5]	FRACTIONS ± 1/32
.XX = ±.02 [0.5]	ANGLES ± 1°
.XXX = ±.005 [0.13]	
CABLE LENGTH TOLERANCES:	
≤12 [305] = +1 [25] / -0	
>12 [305] ≤ 60 [1524] = +2 [51] / -0	
>60 [1524] ≤ 120 [3048] = +4 [102] / -0	
>120 [3048] ≤ 300 [7620] = +6 [152] / -0	
>300 [7620] = +5% / -0	
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE UN-DIMENSIONED/NON-CRITICAL FEATURES MAY VARY IN SIZE AND LOCATION COLORS MAY VARY	

**L-com**  
an INFINIT® brand

Website: [www.L-com.com](http://www.L-com.com)  
Phone: 1.800.341.5266 | 1.978.682.6936



INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5

SCALE NONE SHEET 1 OF 1

DESCRIPTION  
DISPLAYPORT TO HDMI ADAPTER, DISPLAYPORT MALE TO HDMI FEMALE

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	LNAGARAJ	DPHD-D	B

6

5

4

3

2

1