


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
C	ECN 11699: ADD TEMPERATURE RATING	03/03/2022	DGUST



WIRING MAP				
CABLE	"P1"	SIGNAL NAME	COLOR	"P2"
TWISTED PAIR 1	1	ML_LANE 0(p)	BROWN	12
	2	GND	DRAIN	11
	3	ML_LANE 0(n)	WHITE	10
TWISTED PAIR 2	4	ML_LANE 1(p)	RED	9
	5	GND	DRAIN	8
TWISTED PAIR 3	6	ML_LANE 1(n)	WHITE	7
	7	ML_LANE 2(p)	GREEN	6
	8	GND	DRAIN	5
TWISTED PAIR 4	9	ML_LANE 2(n)	WHITE	4
	10	ML_LANE 3(p)	ORANGE	3
	11	GND	DRAIN	2
TWISTED PAIR 5	12	ML_LANE 3(n)	WHITE	1
	13	GND	BROWN	13
	14	GND	RED	14
	15	AUX CH(p)	BLUE	15
	16	GND	DRAIN	16
	17	AUX CH(n)	WHITE	17
	18	HOT PLUG DETECT	YELLOW	18
	19	DP_PWR RETURN	ORANGE	19
	20	N/A	N/C	20
	SHELL	GND	BRAID	SHELL


CABLE: (5) SHIELDED TWISTED PAIR 30AWG WITH 30 AWG DRAIN WIRE.  
(4) 30 AWG SINGLE CONDUCTORS.  
PVC JACKET: BLACK.

PART NUMBER	LENGTH	
	METERS	FEET
DPCAMM-0.5	0.5	1.64
DPCAMM-1	1.0	3.28
DPCAMM-2	2.0	6.56
DPCAMM-3	3.0	9.84

- NOTES:
1. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
  2. CABLE ASSEMBLIES SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
  3. TEMPERATURE RATING: -10° TO +80°.



**REGULATORY COMPLIANCE:**  
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0  ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS ± 1/32 .XX = ± .02 [5]   ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936		
	DRAWN BY	01/14/2011		CATEGORY  <b>AUDIO/VIDEO</b>	
	CHECKED BY	01/14/2011			
APPROVED BY	01/14/2011	PRODUCT DESCRIPTION  <b>DISPLAYPORT CABLE M/M</b>			
THIRD-ANGLE PROJECTION	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	CAGE CODE <b>43321</b>	DWG. NO. <b>DPCAMM-X</b>	REV. <b>C</b>
		SCALE: NONE	CAD FILE: DPCAMM-X.SLDDRW	SHEET 1 OF 1	