


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	9/5/12	D.GRIFFIN
B	ECN 6379: REVISED PACKAGING NOTE, IP RATING, ADDED RoHS	9/27/12	D.FRISIELLO



**NOTES:**



1. CABLE RANGE:  $\phi$ .271 TO  $\phi$ .330  
ASSEMBLED OVERALL LENGTH IS APPROX. 4.06".
2. MATERIAL:  
CONNECTOR: ALUMINUM/ZINC-NICKEL.  
HARDWARE: STAINLESS STEEL.  
SEALS: SILICONE/NITRILE.  
LANYARD: STAINLESS STEEL (NYLON COATED).

**B** 3. RATED IP-68

4. ALL DIMENSIONS ARE FOR REFERENCE ONLY.

**B** 5. COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION LSP-010-1.

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D.FRISIELLO	8/28/12	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY D.GUITADAURO	8/28/12	CATEGORY <b>TELECOM/MODULAR</b>
	APPROVED BY D.GALLAGHER	8/28/12	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION <b>RCP SHLD SELD ZNNI .271-.330DC</b>
COLOR VARIATIONS MAY OCCUR		SIZE <b>A</b> FSCM NO. <b>43321</b> DWG. NO. <b>ECRP5103UB0</b> REV. <b>B</b>	SCALE: NONE CAD FILE: ECRP5103UB0.SLDDRW SHEET 1 OF 1