



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



NOTES:

1. HOUSING IS ABS PLASTIC, COLOR: GRAY.
2. EACH CLUSTER BAR IS INDIVIDUALLY PACKAGED IN A PLASTIC BAG WITH (2) 35mm (1.38) LONG WOOD SCREWS AND (1) PIECE OF DOUBLE SIDED MOUNTING TAPE OF THE SAME LENGTH AS THE ABS HOUSING.
3. EACH CLUSTER BAR HAS A SPECIAL MOUNTING STRAP HAVING APPROXIMATELY 50mm OF VELCRO HOOKS AND 50mm OF FELT. THERE IS A PULL TAB ON THE HOOKS END AND A HEAT SEALED LOOP ON THE FELT END.



STRAP IS LOOPED THROUGH SLOT ON BRACKET OF THIS TELCO CONNECTOR AND HEAT SEALED

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING NUMBER WAS 96-091103	8/24/09	D. CASTRO
B	ECN 7246: DELETED KEYED VERSIONS FROM TABLE, ADD ROHS, NEW FORMAT	1/17/14	D.FRISIELLO

MODEL NUMBER	JACK TYPE	TELCO CONNECTOR
EC806F EC806M	NO KEY NO KEY	FEMALE MALE



WIRE MAP
(IN ACCORDANCE WITH SCHEDULE 0 (USOC) 8 WIRE)

JACK NO.	RJ45 PIN NO.	50 PIN CONNECTOR	JACK NO.	RJ45 PIN NO.	50 PIN CONNECTOR
1	5	26	4	5	38
	4	1		4	13
	3	27		3	39
	6	2		6	14
	2	28		2	40
	7	3		7	15
	8	29		8	41
	1	4		1	16
2	5	30	5	5	42
	4	5		4	17
	3	31		3	43
	6	6		6	18
	2	32		2	44
	7	7		7	19
	8	33		8	45
	1	8		1	20
3	5	34	6	5	46
	4	9		4	21
	3	35		3	47
	6	10		6	22
	2	36		2	48
	7	11		7	23
	8	37		8	49
	1	12		1	24

NO CONNECTIONS TO TELCO CONTACTS 25 & 50



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [.51] .XXX = ±.005 [0.13]	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY TJC	9/11/96			
	CHECKED BY ENG	9/11/96	CATEGORY	TELECOM/MODULAR	
	APPROVED BY AEM	8/26/98	PRODUCT DESCRIPTION	CLSTR BAR 6PRT (8X8)/CN50	
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. EC806M	
		SCALE: NONE	CAD FILE: EC806M.SLDDRW	SHEET 1 OF 1	