


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	08/11/2021	PHOSPODAR





ITEM NO.	LENGTH	
	METER	FEET
FCA-LCST-DPM2P-01	1.0	3.28
FCA-LCST-DPM2P-02	2.0	6.56
FCA-LCST-DPM2P-03	3.0	9.84
FCA-LCST-DPM2P-05	5.0	16.40
FCA-LCST-DPM2P-10	10.0	32.81
FCA-LCST-DPM2P-15	15.0	49.21

#### NOTES:

- LC AND ST CONNECTOR POLISH TYPE: UPC.
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

#### REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0  ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]      FRACTIONS .XX = ± .02 [.5]    ± 1/32 .XXX = ± .005 [.13]    ANGLES ± 1°  THIRD-ANGLE PROJECTION 	APPROVALS	DATE	 <div>50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936</div>				
	DRAWN BY DZINN	08/11/2021		CATEGORY  FIBER OPTICS			
	CHECKED BY DFRISIELLO	08/11/2021					
	APPROVED BY PHOSPODAR	08/11/2021					
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			PRODUCT DESCRIPTION FIBER OPTIC PATCH CABLE LC TO ST DUPLEX 50/125 MULTIMODE OM2 OFNP				
COLOR VARIATIONS MAY OCCUR			SIZE <b>A</b>	CAGE CODE <b>43321</b>	ITEM NO. FCA-LCST-DPM2P	REV. <b>A</b>	
			SCALE: NONE			CAD FILE: FCA-LCST-DPM2P.SLDDRW	SHEET 1 OF 1