


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	09/28/2021	PHOSPODAR



PART NUMBER	LENGTH METER [FEET]
FCA-S2SR-FCALCU-01M	1.0 [3.28]
FCA-S2SR-FCALCU-02M	2.0 [6.56]
FCA-S2SR-FCALCU-03M	3.0 [9.84]
FCA-S2SR-FCALCU-05M	5.0 [16.40]
FCA-S2SR-FCALCU-10M	10.0 [32.81]
FCA-S2SR-FCALCU-15M	15.0 [49.21]

**NOTES:**

- FC CONNECTOR 1 ASSEMBLY POLISH TYPE: APC.  
LC CONNECTOR 1 ASSEMBLY POLISH TYPE: UPC.
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]      FRACTIONS ± 1/32 .XX = ± .02 [.5]      ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS DRAWN BY: MVEERAPPAN CHECKED BY: DFRISIELLO APPROVED BY: PHOSPODAR	DATE 09/28/2021 09/28/2021 09/28/2021	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936		
	THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR		CATEGORY <b>FIBER OPTICS</b>	PRODUCT DESCRIPTION <b>CA FCA-LCU 9/125 SINGLEMODE</b>
		SIZE <b>A</b>	CAGE CODE <b>43321</b>	ITEM NO. <b>FCA-S2SR-FCALCU</b>	REV. <b>A</b>
		SCALE: NONE	CAD FILE: FCA-S2SR-FCALCU.SLDDRW	SHEET 1 OF 1	