


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	INITIAL RELEASE	11/12/07	D.FRISIELLO



MODEL NO.	JACKET COLOR	LENGTH MTR [FT]
FODLC50-RD-01	RED	1 M [3.28 FT]
FODLC50-RD-02	RED	2 M [6.56 FT]
FODLC50-RD-03	RED	3 M [9.84 FT]
FODLC50-RD-04	RED	4 M [13.12 FT]
FODLC50-RD-05	RED	5 M [16.40 FT]
FODLC50-RD-10	RED	10 M [32.81 FT]
FODLC50-RD-15	RED	15 M [49.22 FT]
FODLC50-GR-01	GREEN	1 M [3.28 FT]
FODLC50-GR-02	GREEN	2 M [6.56 FT]
FODLC50-GR-03	GREEN	3 M [9.84 FT]
FODLC50-GR-04	GREEN	4 M [13.12 FT]
FODLC50-GR-05	GREEN	5 M [16.40 FT]
FODLC50-GR-10	GREEN	10 M [32.81 FT]
FODLC50-GR-15	GREEN	15 M [49.22 FT]
FODLC50-BL-01	BLUE	1 M [3.28 FT]
FODLC50-BL-02	BLUE	2 M [6.56 FT]
FODLC50-BL-03	BLUE	3 M [9.84 FT]
FODLC50-BL-04	BLUE	4 M [13.12 FT]
FODLC50-BL-05	BLUE	5 M [16.40 FT]
FODLC50-BL-10	BLUE	10 M [32.81 FT]
FODLC50-BL-15	BLUE	15 M [49.22 FT]
FODLC50-YL-01	YELLOW	1 M [3.28 FT]
FODLC50-YL-02	YELLOW	2 M [6.56 FT]
FODLC50-YL-03	YELLOW	3 M [9.84 FT]
FODLC50-YL-04	YELLOW	4 M [13.12 FT]
FODLC50-YL-05	YELLOW	5 M [16.40 FT]
FODLC50-YL-10	YELLOW	10 M [32.81 FT]
FODLC50-YL-15	YELLOW	15 M [49.22 FT]

NOTES:

CABLE CHARACTERISTICS:
50/125 DUPLEX FIBER ZIPCORD.
JACKET RATING: PVC, OFNR.
JACKET COLOR: SEE CHART.
CABLE O.D: 3.0 mm.

TESTING:
DOUBLE ENDED INSERTION LOSS TEST. CABLES WITH GREATER THAN 1.0 dB OF LOSS ARE REJECTED.

CONNECTOR POLISH: THIS ASSEMBLY UTILIZES A PC POLISH.

MISCELLANEOUS:
OPERATING TEMPERATURE: -20° C TO +70° C.
CABLE ASSEMBLY TO SHIP WITH DUST CAPS INSTALLED. (NOT SHOWN)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]

TOLERANCES TO BE:
.X ±.1 [2.5] ANGLES ±2°
.XX ±.01 [.25]
.XXX ±.005 [.13]

OVERALL CABLE LENGTH TOL:
≤ 60 [1524] +3 [76.2] / -0
> 60 [1524] +5% / -0%

PROJ

APPROVALS	DATE
DRAWN BY D.FRISIELLO	11/12/07
CHECKED BY D.PARHAM	11/12/07
APPROVED BY P.McNEIL	11/12/07

CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY

L-com
CONNECTIVITY PRODUCTS

45 BEECHWOOD DRIVE
NORTH ANDOVER, MA
01845

CATEGORY: FIBER OPTICS

PRODUCT DESCRIPTION: 50/125 LC-LC DPLX ASSEMBLY

SIZE A	FSCM NO. 43321	DWG. NO. FODLC50-COLOR	REV. A
------------------	--------------------------	---------------------------	------------------

SCALE: NONE | CAD FILE: FODLC50-COLOR.SLDDRW | SHEET 1 OF 1