

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	7/13/11	D.GRIFFIN




CHART A					
MODEL NUMBER	LENGTH, M [FT]	COLOR	MODEL NUMBER	LENGTH, M [FT]	COLOR
FPT9OM1-ST-BLK-1	1.0 [3.28]	BLACK	FPT9OM1-ST-AQU-1	1.0 [3.28]	AQUA
FPT9OM1-ST-BLK-2	2.0 [6.56]	BLACK	FPT9OM1-ST-AQU-2	2.0 [6.56]	AQUA
FPT9OM1-ST-BLK-3	3.0 [9.84]	BLACK	FPT9OM1-ST-AQU-3	3.0 [9.84]	AQUA
FPT9OM1-ST-ORG-1	1.0 [3.28]	ORANGE	FPT9OM1-ST-BRN-1	1.0 [3.28]	BROWN
FPT9OM1-ST-ORG-2	2.0 [6.56]	ORANGE	FPT9OM1-ST-BRN-2	2.0 [6.56]	BROWN
FPT9OM1-ST-ORG-3	3.0 [9.84]	ORANGE	FPT9OM1-ST-BRN-3	3.0 [9.84]	BROWN
FPT9OM1-ST-YLW-1	1.0 [3.28]	YELLOW	FPT9OM1-ST-RED-1	1.0 [3.28]	RED
FPT9OM1-ST-YLW-2	2.0 [6.56]	YELLOW	FPT9OM1-ST-RED-2	2.0 [6.56]	RED
FPT9OM1-ST-YLW-3	3.0 [9.84]	YELLOW	FPT9OM1-ST-RED-3	3.0 [9.84]	RED
FPT9OM1-ST-GRY-1	1.0 [3.28]	GRAY	FPT9OM1-ST-WHT-1	1.0 [3.28]	WHITE
FPT9OM1-ST-GRY-2	2.0 [6.56]	GRAY	FPT9OM1-ST-WHT-2	2.0 [6.56]	WHITE
FPT9OM1-ST-GRY-3	3.0 [9.84]	GRAY	FPT9OM1-ST-WHT-3	3.0 [3.84]	WHITE
FPT9OM1-ST-BLU-1	1.0 [3.28]	BLUE	FPT9OM1-ST-VIO-1	1.0 [3.28]	VIOLET
FPT9OM1-ST-BLU-2	2.0 [6.56]	BLUE	FPT9OM1-ST-VIO-2	2.0 [6.56]	VIOLET
FPT9OM1-ST-BLU-3	3.0 [9.84]	BLUE	FPT9OM1-ST-VIO-3	3.0 [3.84]	VIOLET
FPT9OM1-ST-GRN-1	1.0 [3.28]	GREEN	FPT9OM1-ST-ROS-1	1.0 [3.28]	ROSE
FPT9OM1-ST-GRN-2	2.0 [6.56]	GREEN	FPT9OM1-ST-ROS-2	2.0 [6.56]	ROSE
FPT9OM1-ST-GRN-3	3.0 [9.84]	GREEN	FPT9OM1-ST-ROS-3	3.0 [9.84]	ROSE

NOTES:

1. ST CONNECTOR ASSEMBLY POLISH TYPE: PC.
2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	APPROVALS DRAWN BY D.FRISIELLO CHECKED BY D.GUITADAURO APPROVED BY D.GALLAGHER	DATE 7/7/11 7/7/11 7/7/11	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
		DWG. NO. FPT9OM1-ST	REV. A
		SCALE: NONE	CAD FILE: FPT9OM1-ST.SLDDRW
		SHEET 1 OF 1	