



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS |                 |         |           |
|-----------|-----------------|---------|-----------|
| REV       | DESCRIPTION     | DATE    | APPROVED  |
| A         | INITIAL RELEASE | 9/15/11 | D.GRIFFIN |
|           |                 |         |           |
|           |                 |         |           |



NOTES:

- PANEL MATERIAL: .06 THK COLD ROLLED STEEL  
FASTENER MATERIAL: THERMOPLASTIC.
- FINISH: BLACK POWDER COAT.
- RECOMMENDED MOUNTING HOLE FOR MATING FASTENER,  $\phi .252 +.002/-0.000$
- SUPPLIED WITH DUST CAPS ON COUPLERS. (NOT SHOWN)
- COMPONENT ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**RoHS Compliant** ✓

|  |   |                                       |  |
|--|---|---------------------------------------|--|
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONS ARE IN INCHES [mm]<br>OVERALL CABLE LENGTH TOLERANCE:<br>$\leq 12$ [305] = +1 [25] / -0<br>$>12$ [305] $\leq 60$ [1524] = +2 [51] / -0<br>$>60$ [1524] $\leq 120$ [3048] = +4 [102] / -0<br>$>120$ [3048] $\leq 300$ [7620] = +6 [152] / -0<br>$>300$ [7620] = +3% / -0%<br>ALL OTHER DIMENSIONAL TOLERANCES:<br>.X = $\pm .2$<br>.XX = $\pm .02$<br>.XXX = $\pm .005$ | APPROVALS<br>DRAWN BY<br>D.FRISIELLO<br>CHECKED BY<br>M.SEDLESKI<br>APPROVED BY<br>M.MARTINEZ | DATE<br>9/13/11<br>9/13/11<br>9/13/11 | 45 BEECHWOOD DRIVE<br>NORTH ANDOVER, MA<br>01845 |
|  | CONFIGURATION DETAILS OF<br>UNDIMENSIONED FEATURES<br>MAY VARY                                |                                       |  |
| PROJECTION<br>   | COLOR VARIATIONS<br>MAY OCCUR   | SIZE<br><b>A</b>                      | FSCM NO.<br><b>43321</b>                         |
|  |   | DWG. NO.<br><b>FSP-SCD6-APC</b>       | REV.<br><b>A</b>                                 |
|  |   | SCALE: NONE                           | CAD FILE: FSP-SCD6-APC.SLDDRW                    |
|  |   | SHEET 1 OF 1                          |  |

