
8 7 6 5

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS |                 |            |           |  |  |  |  |
|-----------|-----------------|------------|-----------|--|--|--|--|
| REV       | DESCRIPTION     | DATE       | APPROVED  |  |  |  |  |
| Α         | INITIAL RELEASE | 07/09/2020 | PHOSPODAR |  |  |  |  |
|           |                 |            |           |  |  |  |  |
|           |                 |            |           |  |  |  |  |
|           |                 |            |           |  |  |  |  |

| PART NUMBER      | FIBER MODE                                    | JACKET TYPE        | CONNECTOR<br>POLISH | BOOT<br>COLOR | JACKET<br>COLOR   | METERS [FEET] |  |
|------------------|-----------------------------------------------|--------------------|---------------------|---------------|-------------------|---------------|--|
| FPT12-SCUSM-BL-3 | SL-3 9/125 SINGLE MODE OS2 OFNR (RISER) RATED |                    | U (ULTRA)           | BLUE          | YELLOW 3.0 [9.84] |               |  |
| FPT12-SCASM-GR-3 | 9/125 SINGLE MODE OS2                         | OFNR (RISER) RATED | A (ANGLE)           | GREEN         | YELLOW            | 3.0 [9.84]    |  |
| FPT12-SCUM3-AQ-3 | 50/125 MULTIMODE OM3                          | OFNR (RISER) RATED | U (ULTRA)           | BLUE          | AQUA              | 3.0 [9.84]    |  |



| WIR     | ING MAP  |  |  |  |  |
|---------|----------|--|--|--|--|
| FIBER # | SC COLOR |  |  |  |  |
| 1       | BLUE     |  |  |  |  |
| 2       | ORANGE   |  |  |  |  |
| 3       | GREEN    |  |  |  |  |
| 4       | BROWN    |  |  |  |  |
| 5       | GRAY     |  |  |  |  |
| 6       | WHITE    |  |  |  |  |
| 7       | RED      |  |  |  |  |
| 8       | BLACK    |  |  |  |  |
| 9       | YELLOW   |  |  |  |  |
| 10      | PURPLE   |  |  |  |  |
| 11      | ROSE     |  |  |  |  |
| 12      | AQUA     |  |  |  |  |
|         |          |  |  |  |  |

## NOTES:

D

- 1. SEE CHART FOR PART NUMBERS, FIBER MODES, JACKET TYPES, COLORS, AND LENGTHS.
- 2. SC CONNECTOR ASSEMBLY POLISH TYPE: SEE CHART
- 3. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- 4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPECIFICATION PS-0031.

|   | UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONS ARE IN INCHES [mm]                  | APPROVALS                                                      | DATE       | 50 High Street, West Mill, North Andover, MA 0184           |                   |          |                   |                                 |         |      |
|---|-------------------------------------------------------------------------------|----------------------------------------------------------------|------------|-------------------------------------------------------------|-------------------|----------|-------------------|---------------------------------|---------|------|
|   | OVERALL CABLE LENGTH TOLERANCE:<br>≤12 [305] = +1 [25] / -0                   | DRAWN BY<br>DFRISIELLO                                         | 07/09/2020 |                                                             |                   |          | brand             | Phone: 1.800.341.<br>1.978.682. |         |      |
|   | >12 [305] ≤60 [1524] = +2 [51] / -0<br>>60 [1524] ≤120 [3048] = +4 [102] / -0 | CHECKED BY<br>PHOSPODAR                                        | 07/09/2020 | CATEGO                                                      | RY                |          |                   |                                 |         |      |
|   | >120 [3048] <300 [7620] = +6 [152] / -0<br>>300 [7620] = +5% / -0             | APPROVED BY<br>PHOSPODAR                                       | 07/09/2020 | FIBER OPTICS                                                |                   |          |                   |                                 |         |      |
|   | $ \begin{array}{llllllllllllllllllllllllllllllllllll$                         | CONFIGURATION DETAILS OF<br>UNDIMENSIONED FEATURES<br>MAY VARY |            | PRODUCT DESCRIPTION  12 Fiber SC Distribution Style Pigtail |                   |          |                   |                                 |         |      |
|   | THIRD-ANGLE PROJECTION                                                        | COLOR VARIATIONS<br>MAY OCCUR                                  |            | SIZE CAGE CODE 43321                                        |                   | FPT12-SC |                   |                                 | A REV.  |      |
|   | 9)                                                                            |                                                                |            | SCALE:                                                      | SCALE: NONE CAD F |          | ILE: FPT12-SC.SLD | DDRW                            | SHEET 1 | OF 1 |
| 1 |                                                                               | 3                                                              |            | 2                                                           |                   |          | 1                 |                                 |         |      |