



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	8/26/11	D.GRIFFIN
B	ECN 5767: ROTATED COUPLERS 180°	10/11/11	D. CASTRO



- NOTES:
- PANEL MATERIAL: .06 THK COLD ROLLED STEEL.
FASTENER MATERIAL: THERMOPLASTIC.
 - FINISH: BLACK POWDER COAT.
 - RECOMMENDED MOUNTING HOLE FOR MATING FASTENER $\phi .252 + .002 / -.000$
 - SUPPLIED WITH DUST CAPS (NOT SHOWN).
 - COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = $\pm .2$.XX = $\pm .02$.XXX = $\pm .005$	APPROVALS DRAWN BY D. CASTRO CHECKED BY D. PARHAM APPROVED BY M. MARTINEZ	DATE 8/23/11 8/23/11 8/23/11	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	CATEGORY FIBER OPTIC SUB PANELS		PRODUCT DESCRIPTION FBR SBPNL 6 SC DPX CPL CR 12 P
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321 DWG. NO. FSP-SCD6-CR	REV. B
SCALE: NONE		CAD FILE: FSP-SCD6-CR.SLDDRW		SHEET 1 OF 1