



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|-----------------|------------|----------|
| REV. | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE | 03/02/2022 | KHIETPAS |

| PARTS LIST | | | |
|------------|---------------|-----|--|
| ITEM NO. | PART NO. | QTY | DESCRIPTION |
| 1 | HG906UP-NF | 1 | ANTOMNI 900MHZ 6DBI |
| 2 | CA4NMLPRSM020 | 1 | N MALE BULKHEAD LIGHTNING PROTECTOR TO RP SMA PL |
| 3 | HT-TAPE104 | 1 | TLCOAX-SEAL SELF-HEALING TAP |

| | | | |
|---|--|---|--|
| <p>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</p> <p>OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +5% / -0</p> <p>ALL OTHER DIMENSIONAL TOLERANCES: .X = $\pm .2$ [5] FRACTIONS $\pm 1/32$.XX = $\pm .02$ [.5] ANGLES $\pm 1^\circ$.XXX = $\pm .005$ [.13]</p> <p>THIRD-ANGLE PROJECTION</p>  | <p>APPROVALS</p> <p>DATE</p> |  <p>50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936</p> | |
| | <p>DRAWN BY AKRESOWSK</p> <p>CHECKED BY DDICKENS</p> <p>APPROVED BY KHIETPAS</p> | | <p>03/02/2022</p> <p>03/02/2022</p> <p>03/02/2022</p> |
| | <p>CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY</p> <p>CATEGORY</p> | | <p>ANTENNAS</p> |
| | <p>COLOR VARIATIONS MAY OCCUR</p> <p>PRODUCT DESCRIPTION</p> | | <p>ANTOMNI 900MHZ 6DBI CARP-SMA M/NM LIGHTNING PROTECTOR, 20 FT CA-400</p> |
| <p>SIZE</p> <p>A</p> | <p>CAGE CODE</p> <p>43321</p> | <p>ITEM NO.</p> <p>LCANKIT1007</p> | <p>REV.</p> <p>A</p> |
| SCALE: NONE | | CAD FILE: LCANKIT1007.SLDDRW | SHEET 1 OF 1 |