


WIRING MAP				
REF DES	2X12	COLOR	1X24	REF DES
J2	1	BLUE	1	J1
	2	ORANGE	2	
	3	GREEN	3	
	4	BROWN	4	
	5	GRAY	5	
	6	WHITE	6	
	7	RED	7	
	8	BLACK	8	
	9	YELLOW	9	
	10	PURPLE	10	
	11	ROSE	11	
	12	AQUA	12	
J3	1	BLUE/BLACK	13	
	2	ORANGE/BLACK	14	
	3	GREEN/BLACK	15	
	4	BROWN/BLACK	16	
	5	GRAY/BLACK	17	
	6	WHITE/BLACK	18	
	7	RED/BLACK	19	
	8	BLACK / WHITE	20	
	9	YELLOW/BLACK	21	
	10	PURPLE/BLACK	22	
	11	ROSE/BLACK	23	
	12	AQUA/BLACK	24	

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	03/28/19	PHOSPODAR



PART NUMBER	METERS (FEET)
MPF24-MPF212OM5Z-1	1.0 (3.28)
MPF24-MPF212OM5Z-3	3.0 (9.84)
MPF24-MPF212OM5Z-5	5.0 (16.40)
MPF24-MPF212OM5Z-10	10.0 (32.81)

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

.X=± .2 [5.08]	FRACTIONS
.XX=± .01 [.25]	± 1/32
.XXX=± .005 [.13]	ANGLES ± 1°

ALL DIMENSIONS SHOWN
ARE FOR REFERENCE ONLY.

THIRD-ANGLE PROJECTION

L-com
an INFINITO brand

50 High Street, West Mill, 3rd Floor, Suite #30
North Andover, MA 01845 USA
Phone: 1.800.341.5266 | 1.978.682.6936
Fax: 1.978.689.9484
e-mail: CustomerService@L-com.com

www.L-com.com

SIZE	CAGE	DRAWN BY	PART NUMBER	REV
A	43321	DZINN	MPF24-MPF212OM5Z	A

THE INFORMATION AND
DESIGN IN THIS DOCUMENT
IS THE PROPERTY OF
L-COM GLOBAL CONNECTIVITY.
ALL RIGHTS RESERVED.

SHEET	1	OF	1
SCALE	N/A		

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.