


WIRING MAP					
J1	J2	J3	COLOR	J4	J5
12			BLUE	1	
11			ORANGE	2	
10			GREEN	3	
9			BROWN	4	
	12		GRAY	5	
	11		WHITE	6	
	10		RED	7	
	9		BLACK	8	
		12	YELLOW	9	
		11	PURPLE	10	
		10	ROSE	11	
		9	AQUA	12	
4			BLUE/BLACK		1
3			ORANGE/BLACK		2
2			GREEN/BLACK		3
1			BROWN/BLACK		4
	4		GRAY/BLACK		5
	3		WHITE/BLACK		6
	2		RED/BLACK		7
	1		BLACK / WHITE		8
		4	YELLOW/BLACK		9
		3	PURPLE/BLACK		10
		2	ROSE/BLACK		11
		1	AQUA/BLACK		12

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	03/28/2019	PHOSPODAR



PART NUMBER	LENGTH METERS (FEET)	BREAKOUT METERS (FEET)
MPF308-MPF212OM3R-1	1.0 (3.28)	0.3 (1.00)
MPF308-MPF212OM3R-3	3.0 (9.84)	0.6 (2.00)
MPF308-MPF212OM3R-5	5.0 (16.40)	0.6 (2.00)
MPF308-MPF212OM3R-10	10.0 (32.81)	0.6 (2.00)

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

X±.2 [5.08]	FRACTIONS ± 1/32
.XX±.01 [.25]	ANGLES ± 1°
.XXX±.005 [.13]	

ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.

THIRD-ANGLE PROJECTION

L-com
an INFINITO brand

50 High Street, West Mill, 3rd Floor, Suite #30
North Andover, MA 01845 USA.
Phone: 1.800.341.5266 | 1.978.682.6936
Fax: 1.978.689.9484
e-mail: CustomerService@L-com.com

www.L-com.com

SIZE	CAGE	DRAWN BY	PART NUMBER	REV
A	43321	DZINN	MPF308-MPF212OM3R	A

THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF L-COM GLOBAL CONNECTIVITY. ALL RIGHTS RESERVED.

SHEET 1 OF 1

SCALE N/A

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.