


WIRING MAP			
J1	COLOR	J2	J3
1	BLUE	1	
2	ORANGE	2	
3	GREEN	3	
4	BROWN	4	
5	GRAY	5	
6	WHITE	6	
7	RED	7	
8	BLACK	8	
9	YELLOW	9	
10	PURPLE	10	
11	ROSE	11	
12	AQUA	12	
13	BLUE/BLACK		1
14	ORANGE/BLACK		2
15	GREEN/BLACK		3
16	BROWN/BLACK		4
17	GRAY/BLACK		5
18	WHITE/BLACK		6
19	RED/BLACK		7
20	BLACK / WHITE		8
21	YELLOW/BLACK		9
22	PURPLE/BLACK		10
23	ROSE/BLACK		11
24	AQUA/BLACK		12

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	03/28/19	PHOSPODAR



PART NUMBER	METERS (FEET)
MPM24-MPM212OM3Z-1	1.0 (3.28)
MPM24-MPM212OM3Z-3	3.0 (9.84)
MPM24-MPM212OM3Z-5	5.0 (16.40)
MPM24-MPM212OM3Z-10	10.0 (32.81)

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS	
TOLERANCES:	
X±.2 [5.08]	FRACTIONS ± 1/32
.XX±.01 [.25]	ANGLES ± 1°
.XXX±.005 [.13]	
ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.	
THIRD-ANGLE PROJECTION	

L-com
an INFINITO® brand
50 High Street, West Mill, 3rd Floor, Suite #30
North Andover, MA 01845 USA
Phone: 1.800.341.5266 | 1.978.682.6936
Fax: 1.978.689.9484
www.L-com.com | e-mail: CustomerService@L-com.com

SIZE	CAGE	DRAWN BY	PART NUMBER	REV
A	43321	DZINN	MPM24-MPM212OM3Z	A

THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF L-COM GLOBAL CONNECTIVITY. ALL RIGHTS RESERVED.	
SHEET	OF
1	1
SCALE	N/A