


WIRING MAP					
J1	J2	J3	COLOR	J4	J5
12			BLUE	1	
11			ORANGE	2	
10			GREEN	3	
9			BROWN	4	
	12		GRAY	5	
	11		WHITE	6	
	10		RED	7	
	9		BLACK	8	
		9	YELLOW	9	
		10	PURPLE	10	
		11	ROSE	11	
		12	AQUA	12	
4			BLUE/BLACK	1	
3			ORANGE/BLACK	2	
2			GREEN/BLACK	3	
1			BROWN/BLACK	4	
	4		GRAY/BLACK	5	
	3		WHITE/BLACK	6	
	2		RED/BLACK	7	
	1		BLACK / WHITE	8	
		4	YELLOW/BLACK	9	
		3	PURPLE/BLACK	10	
		2	ROSE/BLACK	11	
		1	AQUA/BLACK	12	

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	03/28/19	PHOSPODAR



PART NUMBER	METERS (FEET)
MPM308-MPM212OM4R-1	1.0 (3.28)
MPM308-MPM212OM4R-3	3.0 (9.84)
MPM308-MPM212OM4R-5	5.0 (16.40)
MPM308-MPM212OM4R-10	10.0 (32.81)

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

X±.2 [5.08]	FRACTIONS
.XX±.01 [.25]	± 1/32
.XXX±.005 [.13]	ANGLES ± 1°

ALL DIMENSIONS SHOWN
ARE FOR REFERENCE ONLY.

THIRD-ANGLE PROJECTION

L-com
an INFINITO brand

50 High Street, West Mill, 3rd Floor, Suite #30
North Andover, MA 01845 USA
Phone: 1.800.341.5266 | 1.978.682.6936
Fax: 1.978.689.9484
e-mail: CustomerService@L-com.com

www.L-com.com

SIZE	CAGE	DRAWN BY	PART NUMBER	REV
A	43321	DZINN	MPM308-MPM212OM4R	A

THE INFORMATION AND
DESIGN IN THIS DOCUMENT
IS THE PROPERTY OF
L-COM GLOBAL CONNECTIVITY.
ALL RIGHTS RESERVED.

SHEET 1 OF 1

SCALE N/A

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.