


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	06/08/2011	D.GALLAGHER
B	ECN 9791:UPD O/A LENGTH MEASURE LOCATION AND O/A LENGTH TOL.	04/12/2019	GUTTADAURO
C	ECN 10186 CHANGE LABEL TO GENERIC P/N	10/31/2019	GUTTADAURO
D	ECN 10713: JACKET COLOR FROM GRAY TO WHITE, REMOVED -02, -10	09/30/2020	GUTTADAURO



CABLE, CAT 5e, CMR  
24 UTP, 24AWG SOLID  
PVC JACKET, WHITE

GENERIC P/N  
2210 CM

CABLE LABEL DETAIL  
(SEE NOTE 2)

PART NUMBER	LENGTH		CABLE LENGTH TOLERANCE MM[INCHES]
	METERS	FEET	
MRJ21AD-01	1.0	3.28	+100[3.90]/-0[0.00]
MRJ21AD-03	3.0	9.84	+150[5.91]/-0[0.00]
MRJ21AD-05	5.0	16.41	+150[5.91]/-0[0.00]


- NOTE
1. LABELS LOCATED APPROXIMATELY AS SHOWN.
  2. CABLES ≤ 4.5m HAVE ONE CABLE LABEL ONLY.
  3. SEE SHEET 2 FOR WIRING MAP.
  4. OVERALL LENGTH TOLERANCE SEE TABLE
  5. CABLE SHALL BE TESTED FOR CONTINUITY.
  6. CABLE SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
  7. MRJ21 IS A REGISTERED TRADEMARK OF TYCO ELECTRONICS CORPORATION.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0  ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]      FRACTIONS ± 1/32 .XX = ± .02 [5]    ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS D.PARHAM GUTTADAURO D.GALLAGHER	DATE 05/11/2011 05/20/2011 05/23/2011	 an INFINIT® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY  COLOR VARIATIONS MAY OCCUR	
SIZE <b>A</b> CAGE CODE <b>43321</b> ITEM NO. <b>MRJ21AD</b>		SCALE: NONE    CAD FILE: MRJ21AD.SLDDRW    SHEET 1 OF 2	

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

WIRING MAP

MRJ21	COLOR	RJ45	PORT	MRJ21	COLOR	RJ45	PORT
1	WHT/BLU	5	1	29	BLK/GRN	5	4
2	BLU/WHT	4		30	GRN/BLK	4	
13	WHT/ORG	3		41	BLK/BRN	3	
14	ORG/WHT	6		42	BRN/BLK	6	
3	WHT/GRN	1		31	BLK/GRY	1	
4	GRN/WHT	2		32	GRY/BLK	2	
15	WHT/BRN	7		43	YEL/BLU	7	
16	BRN/WHT	8		44	BLU/YEL	8	
25	WHT/GRY	5	2	9	YEL/ORG	5	5
26	GRY/WHT	4		10	ORG/YEL	4	
37	RED/BLU	3		21	YEL/GRN	3	
38	BLU/RED	6		22	GRN/YEL	6	
27	RED/ORG	1		11	YEL/BRN	1	
28	ORG/RED	2		12	BRN/YEL	2	
39	RED/GRN	7		23	YEL/GRY	7	
40	GRN/RED	8		24	GRY/YEL	8	
5	RED/BRN	5	3	33	VIO/BLU	5	6
6	BRN/RED	4		34	BLU/VIO	4	
17	RED/GRY	3		45	VIO/ORG	3	
18	GRY/RED	6		46	ORG/VIO	6	
7	BLK/BLU	1		35	VIO/GRN	1	
8	BLU/BLK	2		36	GRN/VIO	2	
19	BLK/ORG	7		47	VIO/BRN	7	
20	ORG/BLK	8		48	BRN/VIO	8	

		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
CATEGORY <p style="text-align: center;">TELECOM/MODULAR</p>			
PRODUCT DESCRIPTION <p style="text-align: center;">CA 6X RJ45 MRJ21</p>			
SIZE <b>A</b>	CAGE CODE <b>43321</b>	ITEM NO. <b>MRJ21AD</b>	REV. <b>D</b>
SCALE: NONE		CAD FILE: MRJ21AD.SLDDRW	
			SHEET 2 OF 2