


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED TO PRODUCTION	3/25/02	R. CARRICK
B	ECN #1361 - CHG'D NOTES & TITLE BLOCK	07/15/03	R.CARRICK
C	ECN 99999: CORRECTED COLOR OF COUPLER	3/12/08	D.FRISIELLO
D	ECN 5396: RE-MODELED AND RE-DIMENSIONED	3/22/11	D.FRISIELLO



- NOTES:
1. MATERIAL: .06 THICK COLD ROLLED STEEL.
 2. PANEL FINISH: FLAT BLACK POWDER COAT.
 3. SILKSCREEN COLOR: WHITE.
 4. PANEL ASSEMBLY SHALL BE PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0014.

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS DRAWN BY RON CARRICK	DATE 3/25/2002		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	CHECKED BY DOUG PARHAM	3/25/2002		CATEGORY RACK PANELS		
APPROVED BY C. MCCORMICK	3/25/2002	PRODUCT DESCRIPTION 1U PANEL, W/16 RJ45 SHIELDED COUPLERS				
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. PR175UT568S	REV. D
		SCALE: NONE	CAD FILE: PR175UT568S.SLDDRW		SHEET 1 OF 1	