


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	RELEASED TO PRODUCTION	3/25/02	R. CARRICK
B	ECN #1361 - CHG'D NOTES AND TITLE BLOCK	07/15/03	R. CARRICK
C	ECN 5097: REVISE DESCRIPTION, ADDED NOTE 5 AND NEW FORMAT	10/25/10	D. FRISIELLO
D	5405: RE-MODELED AND RE-DIMENSIONED	3/23/11	D. FRISIELLO



- NOTES:
1. MATERIAL: .06 THICK COLD ROLLED STEEL.
 2. PANEL FINISH: FLAT BLACK POWDER COAT.
 3. SILKSCREEN COLOR: WHITE.
 4. PANEL ASSEMBLY SHALL BE PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0014.

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]

OVERALL CABLE LENGTH TOLERANCE:

- ≤12 [305] = +1 [25] / -0
- >12 [305] ≤60 [1524] = +2[51] / -0
- >60 [1524] ≤120 [3048] = +4 [102] / -0
- >120 [3048] ≤300 [7620] = +6 [152] / -0
- >300 [7620] = +5% / -0%

ALL OTHER DIMENSIONAL TOLERANCES:

- .X = ±.2
- .XX = ±.02
- .XXX = ±.005

PROJECTION

APPROVALS	DATE
DRAWN BY RON CARRICK	3/25/2002
CHECKED BY DOUG PARHAM	3/25/2002
APPROVED BY C. MCCORMICK	3/25/2002

CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY

COLOR VARIATIONS MAY OCCUR

L-com Global Connectivity 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845

CATEGORY: RACK PANELS

PRODUCT DESCRIPTION: 2U PANEL, W/32 RJ45 SHIELDED COUPLERS

SIZE: B	FSCM NO.: 43321	DWG. NO.: PR35UT568S	REV.: D
----------------	------------------------	-----------------------------	----------------

SCALE: 1:2 CAD FILE: PR35UT568S.SLDDRW SHEET 1 OF 1