






THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASEE	03/15/2023	SREITER	AGANWANI

CODING	JACK	COLOR
103		BLACK
104		WHITE
105		BLUE
106		BORDEAUX
107		VIOLET
108		CURRY
109		WATER BLUE



RECOMMENDED
MTG HOLE PATTERN

NOTES:

- ELECTRICAL DATA:
1. IMPEDANCE: 50Ω
 2. FREQUENCY RANGE: DC TO 3GHz
 3. VSWR: 1.35:1

- MECHANICAL:
1. BODY: PLASTIC
 2. CONTACT: BRASS, GOLD PLATED
 3. INSULATION: PTFE

ALL DIMENSIONS FOR REFERENCE ONLY.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</p> <p>OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0</p> <p>ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [13]</p> <p>THIRD-ANGLE PROJECTION</p>	APPROVALS	DATE	 an INFINITI® brand	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	DRAWN BY SREITER	03/15/2023			
	CHECKED BY DWANG	03/30/2023	CATEGORY	PCB CONNECTOR	
	APPROVED BY AGANWANI	03/30/2023	PRODUCT DESCRIPTION	FAKRA PLUG RIGHT ANGLE CONNECTOR SOLDER ATTACHMENT THRU HOLE PCB, BLUE COLOR	
	COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	ITEM NO. RFPCB-FAKRA-MR-4G105	REV. A
		SCALE: NONE	CAD FILE: RFPCB-FAKRA-MR-4G105.SLDDRW	SHEET 1 OF 1	