


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING REPLACES SFODPLC-01-OD1	10/17/14	D. DESJARDIN



PART NUMBER	METERS [FEET]
SFODPLC-01	1.0 [3.28]
SFODPLC-02	2.0 [6.56]
SFODPLC-03	3.0 [9.84]
SFODPLC-04	4.0 [13.12]
SFODPLC-05	5.0 [16.40]

NOTES:

- LC CONNECTOR ASSEMBLY POLISH TYPE: PC
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ± .005 [1.27]	APPROVALS DRAWN BY MCCORMICK CHECKED BY D. PARHAM APPROVED BY R. CARRICK	DATE 12/02/2002 12/02/2002 12/02/2002	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY FIBER OPTICS PRODUCT DESCRIPTION CA LC-LC 9/125 DPLX PLEN			
PROJECTION 	SCALE: NONE CAD FILE: SFODPLC.SLDDRW	SIZE A	FSCM NO. 43321	DWG. NO. SFODPLC	REV. A