



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVAL
B	ECN 10346: ADDED -100, -500, NEW FORMAT	01/29/2020	GUTTADAURO

TFCPUR5730-XXX CONSISTS OF A CONTINUOUS LENGTH OF BULK CABLE





COLOR CODE  
 BLUE x WHITE/BLUE  
 ORANGE x WHITE/ORANGE  
 GREEN x WHITE/GREEN  
 BROWN x WHITE/BROWN

NOTES:

- CONSTRUCTION:  
 CONDUCTOR: 26 AWG STRANDED TINNED COPPER  
 INSULATION MATERIAL: POLYOLEFIN  
 PAIRS: COLOR CODED SINGLES TWISTED INTO PAIRS  
 BINDER: CLEAR POLYESTER TAPE  
 SHIELD: AN ALUMINUM POLYESTER FOIL SHIELD, 100% COVERAGE (FOIL OUT)  
 DRAIN WIRE: 26 AWG TINNED COPPER WIRE  
 OUTER BRAID: TIN PLATED COPPER, 85% COVERAGE  
 JACKET: POLYURETHANE, BLACK  
 O.D: .039" MAX  
 CABLE DIA: 0.220" +/- .010"
- PHYSICAL PROPERTIES:  
 TEMPERATURE RATING: -40° C TO +75° C  
 U.V. RESISTANT JACKET
- AGENCY APPROVALS: CE MARK, RoHS COMPLIANT
- JACKET PRINT:  
 QUABBIN DATAMAX EXTREME DURABLE INDUSTRIAL ETHERNET PATCH CORD CAT 5e SF/UTP P/N 5730 -- CE RoHS --  
 (LOT DESIGNATOR) (SEQUENTIAL FOOTAGE)
- ELECTRICAL CHARACTERISTICS: (FOR 100M OF CABLE)  
 CAPACITANC, MUTUAL NOM. 13.5 PF/FT AT 1 MHZ  
 DIELECTRIC WITHSTANDING, MIN. 1500V RMS  
 VOLTAGE RATING, MAX. 300V  
 D.C. RESISTANCE, MAX. 42.6 OHM/1000 FT  
 IMPEDANCE 100 +/- 15 OHM 1-100 MHZ

MODEL NUMBER	LENGTH	COLOR	PACKAGING
TFCPUR5730	1000.0 FT	BLACK	SPOOL
TFCPUR5730-100	100.0 FT	BLACK	POLY BAG
TFCPUR5730-500	500.0 FT	BLACK	SPOOL

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] - 60 [1524] = +2 [51] / -0 >60 [1524] - 120 [3048] = +4 [102] / -0 >120 [3048] - 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .2 [5.08] .XX = .02 [51] .XXX = .005 [13]	APPROVALS	DATE	 50 HIGH STREET NORTH ANDOVER, MA 01845
	DRAWN BY DFRISIELLO	01/17/2020	
PROJECTION 	CHECKED BY GUTTADAURO	01/29/2020	CATEGORY TELECOM/MODULAR
	APPROVED BY GUTTADAURO	01/29/2020	PRODUCT DESCRIPTION C5e F/UTP 26STR PUR IND OD BLK
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY  COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. TFCPUR5730
SCALE: NONE		CAD FILE: TFCPUR5730.SLDRW	REV. <b>B</b> SHEET 1 OF 1