



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


| REVISION |     |                 |            |            |
|----------|-----|-----------------|------------|------------|
| ZONE     | REV | DESCRIPTION     | DATE       | CHANGED BY |
|          | A   | INITIAL RELEASE | 01/17/2024 | BZHANG     |
|          |     |                 |            | GUTTADAURO |



P1  
RJ45 SHIELDED MODULAR PLUG  
GOLD PLATED CONTACTS  
(8P8C)




POSITION 1  
P2  
RJ45 SHIELDED MODULAR PLUG  
GOLD PLATED CONTACTS  
(8P8C)



#### NOTES:

1. PLUG CONFORMS TO TIA-1096.
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

|                                                                                                                                                                                                                                                                                                                                                                                                                                       |                           |                              |                                                                                                            |  |                                                                                                       |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------|------------------------------|------------------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------|
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONS ARE IN INCHES [mm]<br><br>OVERALL CABLE LENGTH TOLERANCE:<br><br>≤12 [305] = +1 [25] / -0<br>>12 [305] ≤60 [1524] = +2 [51] / -0<br>>60 [1524] ≤120 [3048] = +4 [102] / -0<br>>120 [3048] ≤300 [7620] = +6 [152] / -0<br>>300 [7620] = +5% / -0<br><br>ALL OTHER DIMENSIONAL TOLERANCES:<br>.X = ± .2 [5]      FRACTIONS ± 1/32<br>.XX = ± .02 [.5]      ANGLES ± 1°<br>.XXX = ± .005 [.13] | APPROVALS                 | DATE                         | <br>an INFINITO brand |  | 50 High Street, West Mill,<br>North Andover, MA 01845 USA.<br>Phone: 1.800.341.5266<br>1.978.682.6936 |
|                                                                                                                                                                                                                                                                                                                                                                                                                                       | DRAWN BY<br>BZHANG        | 10/05/2023                   |                                                                                                            |  |                                                                                                       |
|                                                                                                                                                                                                                                                                                                                                                                                                                                       | CHECKED BY<br>GUTTADAURO  | 10/05/2023                   | CATEGORY                                                                                                   |  |                                                                                                       |
|                                                                                                                                                                                                                                                                                                                                                                                                                                       | APPROVED BY<br>GUTTADAURO | 10/05/2023                   | TELECOM/MODULAR                                                                                            |  |                                                                                                       |
| THIRD-ANGLE PROJECTION<br>                                                                                                                                                                                                                                                                                                                       |                           |                              | PRODUCT DESCRIPTION<br><br>C6A PVC F/UTP STR-LFT                                                           |  |                                                                                                       |
| CONFIGURATION DETAILS OF<br>UNDIMENSIONED FEATURES<br>MAY VARY                                                                                                                                                                                                                                                                                                                                                                        |                           |                              | COLOR VARIATIONS<br>MAY OCCUR                                                                              |  |                                                                                                       |
| SIZE<br>A                                                                                                                                                                                                                                                                                                                                                                                                                             |                           | CAGE CODE<br>43321           | ITEM NO.<br>TRD695ASRA6                                                                                    |  | REV.<br>A                                                                                             |
| SCALE: NONE                                                                                                                                                                                                                                                                                                                                                                                                                           |                           | CAD FILE: TRD695ASRA6.SLDDRW |                                                                                                            |  | SHEET 1 OF 2                                                                                          |

8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE  
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE  
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| PART NUMBER       | COLOR | LENGTH<br>FEET [METERS] | PART NUMBER       | COLOR | LENGTH<br>FEET [METERS] | PART NUMBER       | COLOR  | LENGTH<br>FEET [METERS] | PART NUMBER       | COLOR  | LENGTH<br>FEET [METERS] |
|-------------------|-------|-------------------------|-------------------|-------|-------------------------|-------------------|--------|-------------------------|-------------------|--------|-------------------------|
| TRD695ASRA6BLK-1  | BLACK | 1.0 [0.30]              | TRD695ASRA6RED-1  | RED   | 1.0 [0.30]              | TRD695ASRA6GRY-1  | GRAY   | 1.0 [0.30]              | TRD695ASRA6YEL-1  | YELLOW | 1.0 [0.30]              |
| TRD695ASRA6BLK-2  | BLACK | 2.0 [0.61]              | TRD695ASRA6RED-2  | RED   | 2.0 [0.61]              | TRD695ASRA6GRY-2  | GRAY   | 2.0 [0.61]              | TRD695ASRA6YEL-2  | YELLOW | 2.0 [0.61]              |
| TRD695ASRA6BLK-3  | BLACK | 3.0 [0.91]              | TRD695ASRA6RED-3  | RED   | 3.0 [0.91]              | TRD695ASRA6GRY-3  | GRAY   | 3.0 [0.91]              | TRD695ASRA6YEL-3  | YELLOW | 3.0 [0.91]              |
| TRD695ASRA6BLK-5  | BLACK | 5.0 [1.52]              | TRD695ASRA6RED-5  | RED   | 5.0 [1.52]              | TRD695ASRA6GRY-5  | GRAY   | 5.0 [1.52]              | TRD695ASRA6YEL-5  | YELLOW | 5.0 [1.52]              |
| TRD695ASRA6BLK-7  | BLACK | 7.0 [2.13]              | TRD695ASRA6RED-7  | RED   | 7.0 [2.13]              | TRD695ASRA6GRY-7  | GRAY   | 7.0 [2.13]              | TRD695ASRA6YEL-7  | YELLOW | 7.0 [2.13]              |
| TRD695ASRA6BLK-10 | BLACK | 10.0 [3.05]             | TRD695ASRA6RED-10 | RED   | 10.0 [3.05]             | TRD695ASRA6GRY-10 | GRAY   | 10.0 [3.05]             | TRD695ASRA6YEL-10 | YELLOW | 10.0 [3.05]             |
| TRD695ASRA6BLK-15 | BLACK | 15.0 [4.57]             | TRD695ASRA6RED-15 | RED   | 15.0 [4.57]             | TRD695ASRA6GRY-15 | GRAY   | 15.0 [4.57]             | TRD695ASRA6YEL-15 | YELLOW | 15.0 [4.57]             |
| TRD695ASRA6BLK-20 | BLACK | 20.0 [6.10]             | TRD695ASRA6RED-20 | RED   | 20.0 [6.10]             | TRD695ASRA6GRY-20 | GRAY   | 20.0 [6.10]             | TRD695ASRA6YEL-20 | YELLOW | 20.0 [6.10]             |
|                   |       |                         |                   |       |                         |                   |        |                         |                   |        |                         |
| TRD695ASRA6BLU-1  | BLUE  | 1.0 [0.30]              | TRD695ASRA6GRN-1  | GREEN | 1.0 [0.30]              | TRD695ASRA6ORG-1  | ORANGE | 1.0 [0.30]              |                   |        |                         |
| TRD695ASRA6BLU-2  | BLUE  | 2.0 [0.61]              | TRD695ASRA6GRN-2  | GREEN | 2.0 [0.61]              | TRD695ASRA6ORG-2  | ORANGE | 2.0 [0.61]              |                   |        |                         |
| TRD695ASRA6BLU-3  | BLUE  | 3.0 [0.91]              | TRD695ASRA6GRN-3  | GREEN | 3.0 [0.91]              | TRD695ASRA6ORG-3  | ORANGE | 3.0 [0.91]              |                   |        |                         |
| TRD695ASRA6BLU-5  | BLUE  | 5.0 [1.52]              | TRD695ASRA6GRN-5  | GREEN | 5.0 [1.52]              | TRD695ASRA6ORG-5  | ORANGE | 5.0 [1.52]              |                   |        |                         |
| TRD695ASRA6BLU-7  | BLUE  | 7.0 [2.13]              | TRD695ASRA6GRN-7  | GREEN | 7.0 [2.13]              | TRD695ASRA6ORG-7  | ORANGE | 7.0 [2.13]              |                   |        |                         |
| TRD695ASRA6BLU-10 | BLUE  | 10.0 [3.05]             | TRD695ASRA6GRN-10 | GREEN | 10.0 [3.05]             | TRD695ASRA6ORG-10 | ORANGE | 10.0 [3.05]             |                   |        |                         |
| TRD695ASRA6BLU-15 | BLUE  | 15.0 [4.57]             | TRD695ASRA6GRN-15 | GREEN | 15.0 [4.57]             | TRD695ASRA6ORG-15 | ORANGE | 15.0 [4.57]             |                   |        |                         |
| TRD695ASRA6BLU-20 | BLUE  | 20.0 [6.10]             | TRD695ASRA6GRN-20 | GREEN | 20.0 [6.10]             | TRD695ASRA6ORG-20 | ORANGE | 20.0 [6.10]             |                   |        |                         |
|                   |       |                         |                   |       |                         |                   |        |                         |                   |        |                         |



50 High Street, West Mill,  
North Andover, MA 01845 USA.  
Phone: 1.800.341.5266  
1.978.682.6936

CATEGORY

TELECOM/MODULAR

PRODUCT DESCRIPTION

C6A PVC F/UTP STR-LFT

|      |           |             |      |
|------|-----------|-------------|------|
| SIZE | CAGE CODE | ITEM NO.    | REV. |
| A    | 43321     | TRD695ASRA6 | A    |

|             |                              |              |
|-------------|------------------------------|--------------|
| SCALE: NONE | CAD FILE: TRD695ASRA6.SLDDRW | SHEET 2 OF 2 |
|-------------|------------------------------|--------------|