



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	01/17/2024	BZHANG	GUTTADAURO



P1  
SHIELDED RJ45 MODULAR PLUG  
GOLD PLATED CONTACTS  
(8P8C)



P2  
SHIELDED RJ45 MODULAR PLUG  
GOLD PLATED CONTACTS  
(8P8C)

RIGHT ANGLE MOLDED BOOT  
WITH BOTH SIDES LOGO  
PVC, COLOR: BLACK  
SHIELD: COPPER FOIL




**NOTES:**

1. PLUG CONFORMS TO TIA-1096
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936		
	OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0	DRAWN BY BZHANG		10/05/2023	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]      FRACTIONS ± 1/32 .XX = ± .02 [5]      ANGLES ± 1° .XXX = ± .005 [13]	CHECKED BY GUTTADAURO	10/05/2023	CATEGORY <b>TELECOM/MODULAR</b>		
	APPROVED BY GUTTADAURO	10/05/2023			
THIRD-ANGLE PROJECTION	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION <b>C6A PVC F/UTP STR-RGT</b>			
	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	CAGE CODE <b>43321</b>	ITEM NO. <b>TRD695ASRA7</b>	REV. <b>A</b>
		SCALE: NONE	CAD FILE: TRD695ASRA7.SLDDRW		SHEET 1 OF 2

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD695ASRA7BLK-1	BLACK	1.0 [0.30]	TRD695ASRA7RED-1	RED	1.0 [0.30]	TRD695ASRA7GRY-1	GRAY	1.0 [0.30]	TRD695ASRA7YEL-1	YELLOW	1.0 [0.30]
TRD695ASRA7BLK-2	BLACK	2.0 [0.61]	TRD695ASRA7RED-2	RED	2.0 [0.61]	TRD695ASRA7GRY-2	GRAY	2.0 [0.61]	TRD695ASRA7YEL-2	YELLOW	2.0 [0.61]
TRD695ASRA7BLK-3	BLACK	3.0 [0.91]	TRD695ASRA7RED-3	RED	3.0 [0.91]	TRD695ASRA7GRY-3	GRAY	3.0 [0.91]	TRD695ASRA7YEL-3	YELLOW	3.0 [0.91]
TRD695ASRA7BLK-5	BLACK	5.0 [1.52]	TRD695ASRA7RED-5	RED	5.0 [1.52]	TRD695ASRA7GRY-5	GRAY	5.0 [1.52]	TRD695ASRA7YEL-5	YELLOW	5.0 [1.52]
TRD695ASRA7BLK-7	BLACK	7.0 [2.13]	TRD695ASRA7RED-7	RED	7.0 [2.13]	TRD695ASRA7GRY-7	GRAY	7.0 [2.13]	TRD695ASRA7YEL-7	YELLOW	7.0 [2.13]
TRD695ASRA7BLK-10	BLACK	10.0 [3.05]	TRD695ASRA7RED-10	RED	10.0 [3.05]	TRD695ASRA7GRY-10	GRAY	10.0 [3.05]	TRD695ASRA7YEL-10	YELLOW	10.0 [3.05]
TRD695ASRA7BLK-15	BLACK	15.0 [4.57]	TRD695ASRA7RED-15	RED	15.0 [4.57]	TRD695ASRA7GRY-15	GRAY	15.0 [4.57]	TRD695ASRA7YEL-15	YELLOW	15.0 [4.57]
TRD695ASRA7BLK-20	BLACK	20.0 [6.10]	TRD695ASRA7RED-20	RED	20.0 [6.10]	TRD695ASRA7GRY-20	GRAY	20.0 [6.10]	TRD695ASRA7YEL-20	YELLOW	20.0 [6.10]
TRD695ASRA7BLU-1	BLUE	1.0 [0.30]	TRD695ASRA7GRN-1	GREEN	1.0 [0.30]	TRD695ASRA7ORG-1	ORANGE	1.0 [0.30]			
TRD695ASRA7BLU-2	BLUE	2.0 [0.61]	TRD695ASRA7GRN-2	GREEN	2.0 [0.61]	TRD695ASRA7ORG-2	ORANGE	2.0 [0.61]			
TRD695ASRA7BLU-3	BLUE	3.0 [0.91]	TRD695ASRA7GRN-3	GREEN	3.0 [0.91]	TRD695ASRA7ORG-3	ORANGE	3.0 [0.91]			
TRD695ASRA7BLU-5	BLUE	5.0 [1.52]	TRD695ASRA7GRN-5	GREEN	5.0 [1.52]	TRD695ASRA7ORG-5	ORANGE	5.0 [1.52]			
TRD695ASRA7BLU-7	BLUE	7.0 [2.13]	TRD695ASRA7GRN-7	GREEN	7.0 [2.13]	TRD695ASRA7ORG-7	ORANGE	7.0 [2.13]			
TRD695ASRA7BLU-10	BLUE	10.0 [3.05]	TRD695ASRA7GRN-10	GREEN	10.0 [3.05]	TRD695ASRA7ORG-10	ORANGE	10.0 [3.05]			
TRD695ASRA7BLU-15	BLUE	15.0 [4.57]	TRD695ASRA7GRN-15	GREEN	15.0 [4.57]	TRD695ASRA7ORG-15	ORANGE	15.0 [4.57]			
TRD695ASRA7BLU-20	BLUE	20.0 [6.10]	TRD695ASRA7GRN-20	GREEN	20.0 [6.10]	TRD695ASRA7ORG-20	ORANGE	20.0 [6.10]			

		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
CATEGORY <p style="text-align: center;"><b>TELECOM/MODULAR</b></p>			
PRODUCT DESCRIPTION <p style="text-align: center;"><b>C6A PVC F/UTP STR-RGT</b></p>			
SIZE <b>A</b>	CAGE CODE <b>43321</b>	ITEM NO. <b>TRD695ASRA7</b>	REV. <b>A</b>
SCALE: NONE		CAD FILE: TRD695ASRA7.SLDDRW	
			SHEET 2 OF 2