



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	01/17/2024	BZHANG	GUTTADAURO



**NOTES:**


1. PLUG CONFORMS TO TIA-1096
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**LSZH CABLE CHARACTERISTICS:**  
 FLAME RATING: IEC 60332-1  
 CORROSIVE GAS: IEC 60754  
 SMOKE EMISSION: IEC 61034

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936			
	OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0	DRAWN BY BZHANG		10/05/2023		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS ± 1/32 .XX = ± .02 [.5]   ANGLES ± 1° .XXX = ± .005 [.13]	CHECKED BY GUTTADAURO	10/05/2023	CATEGORY <b>TELECOM/MODULAR</b>			
	APPROVED BY GUTTADAURO	10/05/2023		PRODUCT DESCRIPTION <b>C6A LSZH F/UTP STR-UP</b>		
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	CAGE CODE <b>43321</b>	ITEM NO. <b>TRD695ASZRA2</b>	REV. <b>A</b>
SCALE: NONE		CAD FILE: TRD695ASZRA2.SLDDRW		SHEET 1 OF 2		

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD695ASZRA2BLK-1	BLACK	1.0 [0.30]	TRD695ASZRA2RED-1	RED	1.0 [0.30]	TRD695ASZRA2GRY-1	GRAY	1.0 [0.30]
TRD695ASZRA2BLK-2	BLACK	2.0 [0.61]	TRD695ASZRA2RED-2	RED	2.0 [0.61]	TRD695ASZRA2GRY-2	GRAY	2.0 [0.61]
TRD695ASZRA2BLK-3	BLACK	3.0 [0.91]	TRD695ASZRA2RED-3	RED	3.0 [0.91]	TRD695ASZRA2GRY-3	GRAY	3.0 [0.91]
TRD695ASZRA2BLK-5	BLACK	5.0 [1.52]	TRD695ASZRA2RED-5	RED	5.0 [1.52]	TRD695ASZRA2GRY-5	GRAY	5.0 [1.52]
TRD695ASZRA2BLK-7	BLACK	7.0 [2.13]	TRD695ASZRA2RED-7	RED	7.0 [2.13]	TRD695ASZRA2GRY-7	GRAY	7.0 [2.13]
TRD695ASZRA2BLK-10	BLACK	10.0 [3.05]	TRD695ASZRA2RED-10	RED	10.0 [3.05]	TRD695ASZRA2GRY-10	GRAY	10.0 [3.05]
TRD695ASZRA2BLK-15	BLACK	15.0 [4.57]	TRD695ASZRA2RED-15	RED	15.0 [4.57]	TRD695ASZRA2GRY-15	GRAY	15.0 [4.57]
TRD695ASZRA2BLK-20	BLACK	20.0 [6.10]	TRD695ASZRA2RED-20	RED	20.0 [6.10]	TRD695ASZRA2GRY-20	GRAY	20.0 [6.10]

		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
CATEGORY <p style="text-align: center;"><b>TELECOM/MODULAR</b></p>			
PRODUCT DESCRIPTION <p style="text-align: center;"><b>C6A LSZH F/UTP STR-UP</b></p>			
SIZE <b>A</b>	CAGE CODE <b>43321</b>	ITEM NO. <b>TRD695ASZRA2</b>	REV. <b>A</b>
SCALE: NONE		CAD FILE: TRD695ASZRA2.SLDDRW	
			SHEET 2 OF 2