



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	01/17/2024	BZHANG	GUTTADAURO




NOTES:

1. PLUG CONFORMS TO TIA-1096
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

LSZH CABLE CHARACTERISTICS:

FLAME RATING: IEC 60332-1
CORROSIVE GAS: IEC 60754
SMOKE EMISSION: IEC 61034

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS	DATE	 an INFINIT® brand		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	DRAWN BY BZHANG	10/05/2023				
	CHECKED BY GUTTADAURO	10/05/2023	CATEGORY		TELECOM/MODULAR	
	APPROVED BY GUTTADAURO	10/05/2023	PRODUCT DESCRIPTION		C6A LSZH F/UTP STR-LFT	
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	CAGE CODE 43321	ITEM NO. TRD695ASZRA6	REV. A
	COLOR VARIATIONS MAY OCCUR		SCALE: NONE	CAD FILE: TRD695ASZRA6.SLDDRW		SHEET 1 OF 2

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD695ASZRA6BLK-1	BLACK	1.0 [0.30]	TRD695ASZRA6RED-1	RED	1.0 [0.30]	TRD695ASZRA6GRY-1	GRAY	1.0 [0.30]
TRD695ASZRA6BLK-2	BLACK	2.0 [0.61]	TRD695ASZRA6RED-2	RED	2.0 [0.61]	TRD695ASZRA6GRY-2	GRAY	2.0 [0.61]
TRD695ASZRA6BLK-3	BLACK	3.0 [0.91]	TRD695ASZRA6RED-3	RED	3.0 [0.91]	TRD695ASZRA6GRY-3	GRAY	3.0 [0.91]
TRD695ASZRA6BLK-5	BLACK	5.0 [1.52]	TRD695ASZRA6RED-5	RED	5.0 [1.52]	TRD695ASZRA6GRY-5	GRAY	5.0 [1.52]
TRD695ASZRA6BLK-7	BLACK	7.0 [2.13]	TRD695ASZRA6RED-7	RED	7.0 [2.13]	TRD695ASZRA6GRY-7	GRAY	7.0 [2.13]
TRD695ASZRA6BLK-10	BLACK	10.0 [3.05]	TRD695ASZRA6RED-10	RED	10.0 [3.05]	TRD695ASZRA6GRY-10	GRAY	10.0 [3.05]
TRD695ASZRA6BLK-15	BLACK	15.0 [4.57]	TRD695ASZRA6RED-15	RED	15.0 [4.57]	TRD695ASZRA6GRY-15	GRAY	15.0 [4.57]
TRD695ASZRA6BLK-20	BLACK	20.0 [6.10]	TRD695ASZRA6RED-20	RED	20.0 [6.10]	TRD695ASZRA6GRY-20	GRAY	20.0 [6.10]



50 High Street, West Mill,
North Andover, MA 01845 USA.
Phone: 1.800.341.5266
1.978.682.6936

CATEGORY

TELECOM/MODULAR

PRODUCT DESCRIPTION

C6A LSZH F/UTP STR-LFT

SIZE	CAGE CODE	ITEM NO.	REV.
A	43321	TRD695ASZRA6	A

SCALE: NONE	CAD FILE: TRD695ASZRA6.SLDDRW	SHEET 2 OF 2
-------------	-------------------------------	--------------