



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



| REVISION | | | | | |
|----------|-----|-----------------|------------|------------|------------|
| ZONE | REV | DESCRIPTION | DATE | CHANGED BY | APPROVED |
| | A | INITIAL RELEASE | 01/17/2024 | BZHANG | GUTTADAURO |



NOTES:

1. PLUG CONFORMS TO TIA-1096
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

LSZH CABLE CHARACTERISTICS:
 FLAME RATING: IEC 60332-1
 CORROSIVE GAS: IEC 60754
 SMOKE EMISSION: IEC 61034

| | | | |
|--|---|---------------------------|---|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13] | APPROVALS | DATE |  an INFINITO brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936 |
| | DRAWN BY BZHANG | 10/05/2023 | |
| THIRD-ANGLE PROJECTION  | CHECKED BY GUTTADAURO | 10/05/2023 | CATEGORY TELECOM/MODULAR |
| | APPROVED BY GUTTADAURO | 10/05/2023 | |
| CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | PRODUCT DESCRIPTION C6A LSZH F/UTP STR-UP | | SCALE: NONE CAD FILE: TRD695ASZRA2.SLDDRW SHEET 1 OF 2 |
| COLOR VARIATIONS MAY OCCUR | SIZE A | CAGE CODE 43321 | |

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| PART NUMBER | COLOR | LENGTH FEET [METERS] | PART NUMBER | COLOR | LENGTH FEET [METERS] | PART NUMBER | COLOR | LENGTH FEET [METERS] |
|--------------------|-------|----------------------|--------------------|-------|----------------------|--------------------|-------|----------------------|
| TRD695ASZRA2BLK-1 | BLACK | 1.0 [0.30] | TRD695ASZRA2RED-1 | RED | 1.0 [0.30] | TRD695ASZRA2GRY-1 | GRAY | 1.0 [0.30] |
| TRD695ASZRA2BLK-2 | BLACK | 2.0 [0.61] | TRD695ASZRA2RED-2 | RED | 2.0 [0.61] | TRD695ASZRA2GRY-2 | GRAY | 2.0 [0.61] |
| TRD695ASZRA2BLK-3 | BLACK | 3.0 [0.91] | TRD695ASZRA2RED-3 | RED | 3.0 [0.91] | TRD695ASZRA2GRY-3 | GRAY | 3.0 [0.91] |
| TRD695ASZRA2BLK-5 | BLACK | 5.0 [1.52] | TRD695ASZRA2RED-5 | RED | 5.0 [1.52] | TRD695ASZRA2GRY-5 | GRAY | 5.0 [1.52] |
| TRD695ASZRA2BLK-7 | BLACK | 7.0 [2.13] | TRD695ASZRA2RED-7 | RED | 7.0 [2.13] | TRD695ASZRA2GRY-7 | GRAY | 7.0 [2.13] |
| TRD695ASZRA2BLK-10 | BLACK | 10.0 [3.05] | TRD695ASZRA2RED-10 | RED | 10.0 [3.05] | TRD695ASZRA2GRY-10 | GRAY | 10.0 [3.05] |
| TRD695ASZRA2BLK-15 | BLACK | 15.0 [4.57] | TRD695ASZRA2RED-15 | RED | 15.0 [4.57] | TRD695ASZRA2GRY-15 | GRAY | 15.0 [4.57] |
| TRD695ASZRA2BLK-20 | BLACK | 20.0 [6.10] | TRD695ASZRA2RED-20 | RED | 20.0 [6.10] | TRD695ASZRA2GRY-20 | GRAY | 20.0 [6.10] |



50 High Street, West Mill,
North Andover, MA 01845 USA.
Phone: 1.800.341.5266
1.978.682.6936

CATEGORY

TELECOM/MODULAR

PRODUCT DESCRIPTION

C6A LSZH F/UTP STR-UP

| SIZE | CAGE CODE | ITEM NO. | REV. |
|-------------|--------------|-------------------------------|--------------|
| A | 43321 | TRD695ASZRA2 | A |
| SCALE: NONE | | CAD FILE: TRD695ASZRA2.SLDDRW | SHEET 2 OF 2 |