


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/2/12	D.GRIFFIN
B	ECN6550: ADDED CHANNEL RATING NOTE	3/21/13	D. DESJARDIN
C	ECN 7667: REMOVE CHANNEL RATING NOTE AND ALL LENGTHS OVER 30 FT	11/11/14	D.FRISIELLO



NOTES:

1. PLUG CONFORMS TO TIA-1096
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. DESJARDIN	2/29/12		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ±.005 [1.13]	CHECKED BY J. RUST	3/1/12	CATEGORY TELECOM/MODULAR	
	APPROVED BY D. GALLAGHER	3/1/12	PRODUCT DESCRIPTION C6 PVC UTP LFT-DWN	
PROJECTION 	COLOR VARIATIONS MAY OCCUR		SIZE A	FSCM NO. 43321
			DWG. NO. TRD695RA11	REV. C
			SCALE: NONE	CAD FILE: TRD695RA11.SLDDRW
			SHEET 1 OF 2	

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD695RA11BLK-1	BLACK	1.0 [0.30]	TRD695RA11RD-1	RED	1.0 [0.30]	TRD695RA11GRY-1	GRAY	1.0 [0.30]	TRD695RA11Y-1	YELLOW	1.0 [0.30]
TRD695RA11BLK-2	BLACK	2.0 [0.61]	TRD695RA11RD-2	RED	2.0 [0.61]	TRD695RA11GRY-2	GRAY	2.0 [0.61]	TRD695RA11Y-2	YELLOW	2.0 [0.61]
TRD695RA11BLK-3	BLACK	3.0 [0.91]	TRD695RA11RD-3	RED	3.0 [0.91]	TRD695RA11GRY-3	GRAY	3.0 [0.91]	TRD695RA11Y-3	YELLOW	3.0 [0.91]
TRD695RA11BLK-5	BLACK	5.0 [1.52]	TRD695RA11RD-5	RED	5.0 [1.52]	TRD695RA11GRY-5	GRAY	5.0 [1.52]	TRD695RA11Y-5	YELLOW	5.0 [1.52]
TRD695RA11BLK-7	BLACK	7.0 [2.13]	TRD695RA11RD-7	RED	7.0 [2.13]	TRD695RA11GRY-7	GRAY	7.0 [2.13]	TRD695RA11Y-7	YELLOW	7.0 [2.13]
TRD695RA11BLK-10	BLACK	10.0 [3.05]	TRD695RA11RD-10	RED	10.0 [3.05]	TRD695RA11GRY-10	GRAY	10.0 [3.05]	TRD695RA11Y-10	YELLOW	10.0 [3.05]
TRD695RA11BLK-15	BLACK	15.0 [4.57]	TRD695RA11RD-15	RED	15.0 [4.57]	TRD695RA11GRY-15	GRAY	15.0 [4.57]	TRD695RA11Y-15	YELLOW	15.0 [4.57]
TRD695RA11BLK-20	BLACK	20.0 [6.10]	TRD695RA11RD-20	RED	20.0 [6.10]	TRD695RA11GRY-20	GRAY	20.0 [6.10]	TRD695RA11Y-20	YELLOW	20.0 [6.10]
TRD695RA11BLK-25	BLACK	25.0 [7.62]	TRD695RA11RD-25	RED	25.0 [7.62]	TRD695RA11GRY-25	GRAY	25.0 [7.62]	TRD695RA11Y-25	YELLOW	25.0 [7.62]
TRD695RA11BLK-30	BLACK	30.0 [9.14]	TRD695RA11RD-30	RED	30.0 [9.14]	TRD695RA11GRY-30	GRAY	30.0 [9.14]	TRD695RA11Y-30	YELLOW	30.0 [9.14]
TRD695RA11BL-1	BLUE	1.0 [0.30]	TRD695RA11GR-1	GREEN	1.0 [0.30]	TRD695RA11OR-1	ORANGE	1.0 [0.30]			
TRD695RA11BL-2	BLUE	2.0 [0.61]	TRD695RA11GR-2	GREEN	2.0 [0.61]	TRD695RA11OR-2	ORANGE	2.0 [0.61]			
TRD695RA11BL-3	BLUE	3.0 [0.91]	TRD695RA11GR-3	GREEN	3.0 [0.91]	TRD695RA11OR-3	ORANGE	3.0 [0.91]			
TRD695RA11BL-5	BLUE	5.0 [1.52]	TRD695RA11GR-5	GREEN	5.0 [1.52]	TRD695RA11OR-5	ORANGE	5.0 [1.52]			
TRD695RA11BL-7	BLUE	7.0 [2.13]	TRD695RA11GR-7	GREEN	7.0 [2.13]	TRD695RA11OR-7	ORANGE	7.0 [2.13]			
TRD695RA11BL-10	BLUE	10.0 [3.05]	TRD695RA11GR-10	GREEN	10.0 [3.05]	TRD695RA11OR-10	ORANGE	10.0 [3.05]			
TRD695RA11BL-15	BLUE	15.0 [4.57]	TRD695RA11GR-15	GREEN	15.0 [4.57]	TRD695RA11OR-15	ORANGE	15.0 [4.57]			
TRD695RA11BL-20	BLUE	20.0 [6.10]	TRD695RA11GR-20	GREEN	20.0 [6.10]	TRD695RA11OR-20	ORANGE	20.0 [6.10]			
TRD695RA11BL-25	BLUE	25.0 [7.62]	TRD695RA11GR-25	GREEN	25.0 [7.62]	TRD695RA11OR-25	ORANGE	25.0 [7.62]			
TRD695RA11BL-30	BLUE	30.0 [9.14]	TRD695RA11GR-30	GREEN	30.0 [9.14]	TRD695RA11OR-30	ORANGE	30.0 [9.14]			

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY TELECOM/MODULAR			
PRODUCT DESCRIPTION C6 PVC UTP LFT-DWN			
SIZE A	FSCM NO. 43321	DWG. NO. TRD695RA11	REV. C
SCALE: NONE CAD FILE: TRD695RA11.SLDDRW			SHEET 2 OF 2