



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/3/12	D.GRIFFIN
B	ECN6550: ADDED CHANNEL RATING NOTE	3/20/13	D. DESJARDIN
C	ECN 7667: REMOVE CHANNEL RATING NOTE AND ALL LENGTHS OVER 30 FT	11/10/14	D.FRISIELLO



**WIRING MAP**



**NOTES:**

1. PLUG CONFORMS TO TIA-1096
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] = +1 [25] / -0 $>12$ [305] $\leq 60$ [1524] = +2 [51] / -0 $>60$ [1524] $\leq 120$ [3048] = +4 [102] / -0 $>120$ [3048] $\leq 300$ [7620] = +6 [152] / -0 $>300$ [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = $\pm .2$ [5.08] .XX = $\pm .02$ [51] .XXX = $\pm .005$ [13]	APPROVALS DRAWN BY D.PARHAM CHECKED BY J.RUST APPROVED BY D.GALLAGHER	DATE 02/02/2012 02/02/2012 02/03/2012	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY <b>TELECOM/MODULAR</b>
	PROJECTION 		PRODUCT DESCRIPTION <b>C6 PVC UTP STR-UP</b>
	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD695RA2BLK-1	BLACK	1.0 [0.30]	TRD695RA2RD-1	RED	1.0 [0.30]	TRD695RA2GRY-1	GRAY	1.0 [0.30]	TRD695RA2Y-1	YELLOW	1.0 [0.30]
TRD695RA2BLK-2	BLACK	2.0 [0.61]	TRD695RA2RD-2	RED	2.0 [0.61]	TRD695RA2GRY-2	GRAY	2.0 [0.61]	TRD695RA2Y-2	YELLOW	2.0 [0.61]
TRD695RA2BLK-3	BLACK	3.0 [0.91]	TRD695RA2RD-3	RED	3.0 [0.91]	TRD695RA2GRY-3	GRAY	3.0 [0.91]	TRD695RA2Y-3	YELLOW	3.0 [0.91]
TRD695RA2BLK-5	BLACK	5.0 [1.52]	TRD695RA2RD-5	RED	5.0 [1.52]	TRD695RA2GRY-5	GRAY	5.0 [1.52]	TRD695RA2Y-5	YELLOW	5.0 [1.52]
TRD695RA2BLK-7	BLACK	7.0 [2.13]	TRD695RA2RD-7	RED	7.0 [2.13]	TRD695RA2GRY-7	GRAY	7.0 [2.13]	TRD695RA2Y-7	YELLOW	7.0 [2.13]
TRD695RA2BLK-10	BLACK	10.0 [3.05]	TRD695RA2RD-10	RED	10.0 [3.05]	TRD695RA2GRY-10	GRAY	10.0 [3.05]	TRD695RA2Y-10	YELLOW	10.0 [3.05]
TRD695RA2BLK-15	BLACK	15.0 [4.57]	TRD695RA2RD-15	RED	15.0 [4.57]	TRD695RA2GRY-15	GRAY	15.0 [4.57]	TRD695RA2Y-15	YELLOW	15.0 [4.57]
TRD695RA2BLK-20	BLACK	20.0 [6.10]	TRD695RA2RD-20	RED	20.0 [6.10]	TRD695RA2GRY-20	GRAY	20.0 [6.10]	TRD695RA2Y-20	YELLOW	20.0 [6.10]
TRD695RA2BLK-25	BLACK	25.0 [7.62]	TRD695RA2RD-25	RED	25.0 [7.62]	TRD695RA2GRY-25	GRAY	25.0 [7.62]	TRD695RA2Y-25	YELLOW	25.0 [7.62]
TRD695RA2BLK-30	BLACK	30.0 [9.14]	TRD695RA2RD-30	RED	30.0 [9.14]	TRD695RA2GRY-30	GRAY	30.0 [9.14]	TRD695RA2Y-30	YELLOW	30.0 [9.14]
TRD695RA2BL-1	BLUE	1.0 [0.30]	TRD695RA2GR-1	GREEN	1.0 [0.30]	TRD695RA2OR-1	ORANGE	1.0 [0.30]			
TRD695RA2BL-2	BLUE	2.0 [0.61]	TRD695RA2GR-2	GREEN	2.0 [0.61]	TRD695RA2OR-2	ORANGE	2.0 [0.61]			
TRD695RA2BL-3	BLUE	3.0 [0.91]	TRD695RA2GR-3	GREEN	3.0 [0.91]	TRD695RA2OR-3	ORANGE	3.0 [0.91]			
TRD695RA2BL-5	BLUE	5.0 [1.52]	TRD695RA2GR-5	GREEN	5.0 [1.52]	TRD695RA2OR-5	ORANGE	5.0 [1.52]			
TRD695RA2BL-7	BLUE	7.0 [2.13]	TRD695RA2GR-7	GREEN	7.0 [2.13]	TRD695RA2OR-7	ORANGE	7.0 [2.13]			
TRD695RA2BL-10	BLUE	10.0 [3.05]	TRD695RA2GR-10	GREEN	10.0 [3.05]	TRD695RA2OR-10	ORANGE	10.0 [3.05]			
TRD695RA2BL-15	BLUE	15.0 [4.57]	TRD695RA2GR-15	GREEN	15.0 [4.57]	TRD695RA2OR-15	ORANGE	15.0 [4.57]			
TRD695RA2BL-20	BLUE	20.0 [6.10]	TRD695RA2GR-20	GREEN	20.0 [6.10]	TRD695RA2OR-20	ORANGE	20.0 [6.10]			
TRD695RA2BL-25	BLUE	25.0 [7.62]	TRD695RA2GR-25	GREEN	25.0 [7.62]	TRD695RA2OR-25	ORANGE	25.0 [7.62]			
TRD695RA2BL-30	BLUE	30.0 [9.14]	TRD695RA2GR-30	GREEN	30.0 [9.14]	TRD695RA2OR-30	ORANGE	30.0 [9.14]			

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY <b>TELECOM/MODULAR</b>			
PRODUCT DESCRIPTION <b>C6 PVC UTP STR-UP</b>			
SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>TRD695RA2</b>	REV. <b>C</b>
SCALE: NONE		CAD FILE: TRD695RA2.SLDDRW	
			SHEET 2 OF 2