






THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	6/10/21	DGUTTADAURO



MODEL NUMBER	LENGTH FEET [METERS]
TRD695OS-BLK-1F	1.0 [0.30]
TRD695OS-BLK-3F	3.0 [0.91]
TRD695OS-BLK-5F	5.0 [1.52]
TRD695OS-BLK-10F	10.0 [3.05]
TRD695OS-BLK-15F	15.0 [4.57]
TRD695OS-BLK-25F	25.0 [7.62]
TRD695OS-BLK-50F	50.0 [15.24]
TRD695OS-BLK-75F	75.0 [22.86]
TRD695OS-BLK-100F	100.0 [30.48]
TRD695OS-BLK-150F	150.0 [45.72]
TRD695OS-BLK-200F	200.0 [60.96]
TRD695OS-BLK-250F	250.0 [76.20]



**NOTES:**

CABLE CHARACTERISTICS:  
 TEMPERATURE RATING: -40 °C TO +75 °C  
 VOLTAGE RATING: 600 V  
 FLAME RATING: CMX OUTDOOR - CMR - CMG  
 UL AWM STYLE: 2463  
 CABLE JACKET IS SUNLIGHT (UV) AND CUTTING/MACHINING OIL RESISTANT.

1. PLUG CONFORMS TO TIA-1096
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]      FRACTIONS ± 1/32 .XX = ± .02 [.5]      ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS	DATE	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	DRAWN BY DMAY	6/9/21		CATEGORY <b>TELECOM/MODULAR</b>
	CHECKED BY DGUTTADAURO	6/10/21		
	APPROVED BY DGUTTADAURO	6/10/21		
THIRD-ANGLE PROJECTION	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION <b>C6 F/UTP 23SLD 600V PoE                  CMR-CMX PVC BLK</b>	SIZE <b>A</b> CAGE CODE <b>43321</b> ITEM NO. <b>TRD695OS-BLK</b>	
	COLOR VARIATIONS MAY OCCUR	SCALE: NONE	CAD FILE: TRD695OS-BLK.SLDDRW SHEET 1 OF 1	