




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 10806: ADD LSZH CABLE CHARACTERISTICS TO DWG, NEW FORMAT	11/25/2020	D.Guiffarduro



LSZH CABLE CHARACTERISTICS: 
 FLAME RATING: IEC 60332-1
 CORROSIVE GAS: IEC 60754
 SMOKE EMISSION: IEC 61034


NOTES:

1. PLUG CONFORMS TO TIA-1096
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ± 1/32 .XXX = ± .005 [13] ANGLES ± 1°	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY D.FRISIELLO 1/26/12 CHECKED BY J.RUST 1/26/12 APPROVED BY D.GALLAGHER 1/26/12	CATEGORY TELECOM/MODULAR	
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION C5E LSZ UTP STR-DWN
SCALE: NONE CAD FILE: TRD815ZRA1.SLDDRW	SIZE A	CAGE CODE 43321	ITEM NO. TRD815ZRA1
SHEET 1 OF 2			REV. E

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD815ZRA1BLK-1	BLACK	1.0 [0.30]	TRD815ZRA1RD-1	RED	1.0 [0.30]	TRD815ZRA1GRY-1	GRAY	1.0 [0.30]
TRD815ZRA1BLK-2	BLACK	2.0 [0.61]	TRD815ZRA1RD-2	RED	2.0 [0.61]	TRD815ZRA1GRY-2	GRAY	2.0 [0.61]
TRD815ZRA1BLK-3	BLACK	3.0 [0.91]	TRD815ZRA1RD-3	RED	3.0 [0.91]	TRD815ZRA1GRY-3	GRAY	3.0 [0.91]
TRD815ZRA1BLK-5	BLACK	5.0 [1.52]	TRD815ZRA1RD-5	RED	5.0 [1.52]	TRD815ZRA1GRY-5	GRAY	5.0 [1.52]
TRD815ZRA1BLK-7	BLACK	7.0 [2.13]	TRD815ZRA1RD-7	RED	7.0 [2.13]	TRD815ZRA1GRY-7	GRAY	7.0 [2.13]
TRD815ZRA1BLK-10	BLACK	10.0 [3.05]	TRD815ZRA1RD-10	RED	10.0 [3.05]	TRD815ZRA1GRY-10	GRAY	10.0 [3.05]
TRD815ZRA1BLK-15	BLACK	15.0 [4.57]	TRD815ZRA1RD-15	RED	15.0 [4.57]	TRD815ZRA1GRY-15	GRAY	15.0 [4.57]
TRD815ZRA1BLK-20	BLACK	20.0 [6.10]	TRD815ZRA1RD-20	RED	20.0 [6.10]	TRD815ZRA1GRY-20	GRAY	20.0 [6.10]
TRD815ZRA1BLK-25	BLACK	25.0 [7.62]	TRD815ZRA1RD-25	RED	25.0 [7.62]	TRD815ZRA1GRY-25	GRAY	25.0 [7.62]
TRD815ZRA1BLK-30	BLACK	30.0 [9.14]	TRD815ZRA1RD-30	RED	30.0 [9.14]	TRD815ZRA1GRY-30	GRAY	30.0 [9.14]

		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
CATEGORY <p style="text-align: center;">TELECOM/MODULAR</p>			
PRODUCT DESCRIPTION <p style="text-align: center;">C5E LSZ UTP STR-DWN</p>			
SIZE A	CAGE CODE 43321	ITEM NO. TRD815ZRA1	REV. E
SCALE: NONE		CAD FILE: TRD815ZRA1.SLDDRW	
			SHEET 2 OF 2